


M-12574 1



- NOTES:
- 1. DIMENSIONS ARE INCHES ±.02  
[ mm ] ±.5
  - 2. RATING: 600VAC/250VDC 400 AMP.
  - 3. UL/c-UL ENCLOSURE TYPES 3R, 4X, 12,  
SEE INSTRUCTION SHEET

HUBBELL CAT. NO.	COLOR
HBLMRSCEBK	BLACK
HBLMRSCEW	WHITE
HBLMRSCEGN	GREEN
HBLMRS CER	RED
HBLMRSCEBL	BLUE
HBLMRSCEO	ORANGE
HBLMRSCEBN	BROWN
HBLMRSCEY	YELLOW

LIST OF PARTS

DESCRIPTION	MATERIAL	FINISH
HOUSING	TPE	SEE TABLE
CONTACT	BRASS	
CAGE	NYLON	BLACK
INSERT	BRASS	

DIMENSION SHEET FOR CAT. NO. SEE TABLE

REPAIRABLE  NON-REPAIRABLE

1	INITIAL RELEASE. PER DCN 20483 DDL	DJP	05/02/14
SYM	REVISIONS	APP	DATE

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE  
SINGLE POLE MALE RECEPTACLE W/STUD

TOLERANCES UNLESS OTHERWISE SPECIFIED .XX = ±.01 .XXX = ±.005 ANGLES = ±2°	WIRING DEVICE-KELLEMS HUBBELL INCORPORATED SHELTON, CT	
	DR. BY DDL	APP. BY
	TR. BY	SCALE 1:1
	CHK. BY	DATE 05/02/14

B

M-12574

1