


M-7653 4

DIMENSION SHEET FOR CAT. NO.

GASKET SUPPLIED WITH BLANK PLATE FOR USE IN WET AND DAMP LOCATIONS (TYPE 3R)

LIST OF PARTS		
DESCRIPTION	MATERIAL	FINISH
COVER PLATE, DUPLEX	PBTP	MATTE, GRAY
COVER PLATE, BLANK	PBTP	MATTE, GRAY
COVER PLATE, 1.39 RD	PBTP	MATTE, GRAY
COVER PLATE, 1.56 RD	PBTP	MATTE, GRAY
COVER PLATE, STYLELINE	PBTP	MATTE, GRAY
GASKET	FOAM	
SCREWS	ST STEEL	



DUPLEX
COVER PLATE
HBLP8FS

1.39 RD
COVER PLATE
HBLP7FS

1.56 RD
COVER PLATE
HBLP720FS

STYLELINE
COVER PLATE
HBLP26FS

BLANK
COVER PLATE
HBLP14FS
CAN BE USED FOR
WET AND DAMP LOCATIONS
(TYPE 3R)

4	12/4/01 CONVERTED ALL DIMS. TO mm. ADDED "NOTE" INCHES [mm]. PER DCN 8696 SPN	TCM	12/4/01
3	10-23-96 HBLP7FS (1.39 RD) WAS HBLP26FS & HBLP26FS (STYLELINE) WAS HBLP7FS PER DCN 4658. DJG		10-23-96
2	9-10-96 RELEASED FOR PRODUCTION PER DCN #4443. DJG	KRR	9-10-96
1	"X" REMOVED PER EC 3921	KRR	7-12-96
SYM	REVISIONS	APP	DATE

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE
COVER PLATES
FS AND FD MOUNTING

TOLERANCES UNLESS OTHERWISE SPECIFIED FRACTIONS ± 1/64 DECIMALS ± .020 ANGLES ± 2°	WIRING DEVICE DIVISION HUBBELL, INCORPORATED BRIDGEPORT, CT	
	DR. BY K.R.	APP. BY KRR
	TR. BY	SCALE 1/2
	CHK'D BY KRR	DATE 7-12/96

NOTE: INCHES [mm]

REPAIRABLE

NON-REPAIRABLE

B

M-7653

4