


M-8925 2



- NOTES:
1. DIMENSIONS ARE INCHES  $\pm .02$   
[ mm ]  $\pm .5$
  2. COVER IS SELF CLOSING WHEN INSTALLED
  3. UL/c-UL ENCLOSURE TYPE 3R,  
SEE INSTRUCTION SHEET

HUBBELL CAT. NO.	COLOR
HBLSCBK	BLACK
HBLSCW	WHITE
HBLSCGN	GREEN
HBLSCBR	RED
HBLSCBL	BLUE
HBLSCO	ORANGE
HBLSCBN	BROWN
HBLSCY	YELLOW

LIST OF PARTS		
DESCRIPTION	MATERIAL	FINISH
BACKPLATE	STEEL	ZINC & SEE TABLE
COVER	STEEL	ZINC & SEE TABLE
SPRING	STANLESS	PASSIVATE
HINGE PIN	STEEL	ZINC
FLANGE CAP NUT	STEEL	ZINC
SLEEVE SPACER	NYLON	BLACK
GASKET	CLOSED CELL FOAM	BLACK
LABEL	MYLAR	SILVER

SYMBOL	REVISIONS	APP	DATE
2	UPDATED ASSEMBLY PER DCN 11484 MJM TwB	TwB	1/17/05
1	RELEASED PER DCN 10992 MJM TB	TwB	6/25/03

REPAIRABLE  NON-REPAIRABLE

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE SINGLE POLE SNAP BACK COVER

TOLERANCES UNLESS OTHERWISE SPECIFIED	WIRING DEVICE-KELLEMS HUBBELL INCORPORATED BRIDGEPORT, CT	
FRACTIONS $\pm 1/64$	DR. BY TwB	APP. BY
DECIMALS $\pm .005$	TR. BY	SCALE 1:1
ANGLES $\pm 2'$	CHK'D BY	DATE 6/11/03

DIMENSION SHEET FOR CAT. NO.

REPAIRABLE  NON-REPAIRABLE

B

M-8925

N