

M-12591

2


INSTRUCTION
MANUAL

PN PD2652

LIST OF PARTS

DESCRIPTION	MATERIAL	FINISH
LIGHT HANDLE	PLASTIC	BLACK
LIGHT TUBE	PLASTIC	CLEAR
HANGER	STEEL	PLATED
TOOL TAP		BLACK

DIMENSION SHEET FOR CAT. NO.



NOT DRAWN TO SCALE

FEATURES:
 1-FLOOD LIGHT MODE 120V, 50/60Hz, 0.1A, 6W.
 FOCUSED END BEAM MODE APPROX. 10 DEG.
 120V, 50/60Hz, 0.06A, 3W.
 2-COVERED ON OFF SWITCH IN THE HANDLE.
 3-ETL LISTED

HUBBELL CAT. #	DESCRIPTION	LAMP TYPE	BEAM ANG. DEG.	LUMEN OUTPUT	LIGHT COLOR DEG. KELVIN	LAMP LIFE HR.
HBLWL25LED	LED WORK LIGHT, 25FT, 18/2	HIGH OUTPUT LED	10	920/120	4,700-5,200	50,000
HBLWL25LEDT	LED WORK LIGHT, 25FT, 16/3, TOOL TAP	HIGH OUTPUT LED	10	920/120	4,700-5,200	50,000

2	NOTE 1,FLOOD LIGHT MODE 120V,50/60Hz, 0.1A,6W. FOCUSED END BEAM MODE APPROX.10 DEG.120V, 50/60Hz,0.06A,3W.WAS 9 WATT(2)4 WATT,1 WATT END LIGHT 130 DEG. ANGLE LEOS. REVISED PHOTO. PER DCN 22888.	EM	2/15/17
1	RELEASED PER DCN 20541.	DL	12/19/14
SYM	REVISIONS	APP	DATE

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE
LED LIGHT, WORK LIGHT 25FT

TOLERANCES UNLESS OTHERWISE SPECIFIED .XX = ±.01 .XXX = ±.005 ANGLES = ±2°	WIRING DEVICE-KELLEMS HUBBELL INCORPORATED SHELTON, CT	
	DR. BY MZ	APP. BY DL
	TR. BY	SCALE NONE
	CHK. BY DL	DATE 12/19/14

REPAIRABLE NON-REPAIRABLE

B

M-12591 2