


- NOTES:**
- UL CLASSIFIED/cUL CLASSIFIED AS EQUIPMENT GROUND CONDUCTOR (ONLY PAINTED TRAY cUL CLASSIFIED)
  - \* SUPPORTED AT SIX FOOT SPACING
  - ALL DIMENSIONS ARE ±.25 [6.3]
  - PAINTED TRAY HAS POLYESTER TGIC POWDER COATING
  - 2 X 4 [50.8 X 101.6] MESH OPENING

CAGE CODE 74545

10 FEET PER LENGTH	TRAY WIDTH	LOAD * (Lb/ft)	TRAY AREA (Sq. In.)	WEIGHT PER LENGTH (Lb)	SPLICE QUANTITY*		FINISH	
					90° SWEEP ELBOW	STRAIGHT SPLICE	PRE-GALVANIZED	BLACK POWDER COAT
2 [50.8] DEEP TRAY	4 [101.6]	45	8	7	2	2	HBT0204	HBT0204BK
	6 [152.4] •	50	12	9	3	4	HBT0206	HBT0206BK
	8 [203.2] •	52	16	10.5	4	4	HBT0208	HBT0208BK
	12 [304.8] •	58	24	12	6	4	HBT0212	HBT0212BK
	16 [406.4] •	70	32	15	7	4	HBT0216	HBT0216BK
	18 [457.2] •	70	36	23	9	4	HBT0218	HBT0218BK
	20 [508.0] •	73	40	25	9	5	HBT0220	HBT0220BK
	22 [558.8]	73	44	27	12	5	HBT0222	HBT0222BK
	24 [609.6] •	75	48	31	12	5	HBT0224	HBT0224BK
	26 [660.4]	73	52	33	13	6	HBT0226	HBT0226BK
4 [101.6] DEEP TRAY	4 [101.6]	49	16	12	2	4	HBT0404	HBT0404BK
	6 [152.4] •	49	24	13	3	5	HBT0406	HBT0406BK
	8 [203.2] •	78	32	15	4	6	HBT0408	HBT0408BK
	12 [304.8] •	78	48	23	6	6	HBT0412	HBT0412BK
	16 [406.4] •	108	64	27	7	7	HBT0416	HBT0416BK
	18 [457.2] •	116	72	29	9	7	HBT0418	HBT0418BK
	20 [508.0] •	116	80	31	9	7	HBT0420	HBT0420BK
	22 [558.8]	116	88	33	12	8	HBT0422	HBT0422BK
	24 [609.6] •	116	96	35	12	8	HBT0424	HBT0424BK
	28 [711.2]	108	112	39	14	9	HBT0428	HBT0428BK
6 [152.4] DEEP TRAY	8 [203.2] •	116	48	23	4	6	HBT0608	HBT0608BK
	12 [304.8] •	123	72	27	6	6	HBT0612	HBT0612BK
	16 [406.4] •	123	96	31	7	7	HBT0616	HBT0616BK
	18 [457.2] •	127	108	33	9	7	HBT0618	HBT0618BK
	20 [508.0] •	127	120	35	9	7	HBT0620	HBT0620BK
	22 [558.8] •	127	132	37	12	8	HBT0622	HBT0622BK
8 [203.2] DEEP TRAY	24 [609.6] •	150	144	39	12	8	HBT0624	HBT0624BK
	8 [203.2] •	116	64	27	4	8	HBT0808	HBT0808BK
	12 [304.8] •	116	96	31	6	8	HBT0812	HBT0812BK
	16 [406.4] •	116	128	35	7	9	HBT0816	HBT0816BK
	18 [457.2] •	116	144	37	9	9	HBT0818	HBT0818BK
	20 [508.0] •	116	160	39	9	9	HBT0820	HBT0820BK

LIST OF PARTS		
DESCRIPTION	MATERIAL	FINISH
TRAY	STEEL	SEE TABLE




CATALOG NO. HBT0412 (NOT SHOWN TO SCALE)

1	INITIAL DOCUMENT	DDL	11/15/16
	RELEASE PER DCN 22750		
REV	DESCRIPTION	APP	DATE

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE IN INCHES [mm].

TITLE  
ROUND WIRE BASKET TRAY



TOLERANCES UNLESS OTHERWISE SPECIFIED .XX = ± .01 .XXX = ± .005 ANGLE TOL. ± 2'	DR. BY GM	SCALE	NONE
	CHK. BY MN	DATE	09/07/16

DIMENSION SHEET FOR CAT. NO. M-13467 SEE TABLE B M-13467 1