


OUTSIDE WALL



| TRAY SIZE "D" | TRAY WIDTH "W" | TRAY AREA (Sq. In.) | PRE-GALVANIZED | BLACK POWDER COAT |
|-------------------|-------------------|------------------------|----------------|----------------------|
| 2 [50.8] DEEP | 4 [101.6] | 8 | HBT300204 | HBT300204BK |
| | 6 [152.4] | 12 | HBT300206 | HBT300206BK |
| | 8 [203.2] | 16 | HBT300208 | HBT300208BK |
| | 12 [304.8] | 24 | HBT300212 | HBT300212BK |
| | 16 [406.4] | 32 | HBT300216 | HBT300216BK |
| | 18 [457.2] | 36 | HBT300218 | HBT300218BK |
| | 20 [508.0] | 40 | HBT300220 | HBT300220BK |
| | 24 [609.6] | 48 | HBT300224 | HBT300224BK |
| 4 [101.6] DEEP | 4 [101.6] | 16 | HBT300404 | HBT300404BK |
| | 6 [152.4] | 24 | HBT300406 | HBT300406BK |
| | 8 [203.2] | 32 | HBT300408 | HBT300408BK |
| | 12 [304.8] | 48 | HBT300412 | HBT300412BK |
| | 16 [406.4] | 64 | HBT300416 | HBT300416BK |
| | 18 [457.2] | 72 | HBT300418 | HBT300418BK |
| | 20 [508.0] | 80 | HBT300420 | HBT300420BK |
| | 24 [609.6] | 96 | HBT300424 | HBT300424BK |
| 6 [152.4] DEEP | 8 [203.2] | 48 | HBT300608 | HBT300608BK |
| | 12 [304.8] | 72 | HBT300612 | HBT300612BK |
| | 16 [406.4] | 96 | HBT300616 | HBT300616BK |
| | 18 [457.2] | 108 | HBT300618 | HBT300618BK |
| | 20 [508.0] | 120 | HBT300620 | HBT300620BK |
| | 24 [609.6] | 144 | HBT300624 | HBT300624BK |

NOTES:

1. MOUNTING HARDWARE INCLUDED

| LIST OF PARTS | | | | | | | | |
|---------------|-------------|----------------|--|--|--|--|--|--|
| DESCRIPTION | MATERIAL | FINISH | | | | | | |
| BASE | STEEL | PRE-GLAVANIZED | | | | | | |
| DASE | SIEEL | OR PAINT | | | | | | |
| WALLS | POLYMER | BLACK | | | | | | |
| HARDWARE | STEEL | ZINC PLATED | | | | | | |
| | | | | | | | | |
| | | | | | | | | |
| | | | | | | | | |
| | | | | | | | | |
| | | | | | | | | |
| | | | | | | | | |
| | | | | | | | | |
| | | | | | | | | |
| | | | | | | | | |
| | | | | | | | | |
| | | | | | | | | |
| | | | | | | | | |
| | | | | | | | | |
| CATA | ALOG NO. HE | BT300212 | | | | | | |

CATALOG NO. HBT300212 (NOT SHOWN TO SCALE)

| 1 | INITIAL DOCUMENT | DDL | 11/15/16 |
|-----|-----------------------|-----|----------|
| | RELEASE PER DCN 22750 | | |
| REV | DESCRIPTION | APP | DATE |

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE IN INCHES [mm].

TITLE

PRE-FORMED 30° FITTING



WIRING DEVICE-KELLEMS
HUBBELL INCORPORATED
SHELTON, CT

M-13488

TOLERANCES UNLESS
OTHERWISE SPECIFIED
.XX = ±.01
.XXX= ±.005
ANGLE TOL. ±2

DR. BY GM SCALE NONE CHK. BY MN DATE 09/07/16

CAGE CODE 74545