



M-7075 3

LIST OF PARTS		
DESCRIPTION	MATERIAL	FINISH
BASE	POLYCARBONATE	
COVER	POLYCARBONATE	
GROUND TERMINAL	STEEL	NICKEL PLATE
LINE TERMINAL	BRASS	
DRIVE SCREW	STEEL	ZINC PLATE
14 AWG LEAD WIRE	COPPER	GREEN
HEX HEAD SCREW	STEEL	GREEN
TERMINAL SCREWS	BRASS	

SUPERSEDES DRAWING DATED 5-29-92

SYM	REVISIONS	APP	DATE
4	ADDED CATALOG NO. HBL420HRS TO TABLE PER DCN 19158 MYA	EJM	10/19/12
3	REDRAWN ON CAD ON UPDATED FORMAT WITH CHANGES. DWG. SCALE "NONE" WAS 1:1. ADDED DUAL DIMENSIONING, NOTES 1-3, AND TABLE. ALSO ADDED PARTS TO LIST OF PARTS AND CALL-OUT "GREEN DOT HG ONLY", PER DCN #13355. JMN	DJP	2/2/07

NOTES: (UNLESS OTHERWISE SPECIFIED):

- 1) DIMENSIONS ARE: INCHES [MM]
- 2) XX TOLERANCE TO BE ±.03 [0.76]
- 3) IG STICKER SUPPLIED WITH PRODUCT FOR ISOLATED GROUND APPLICATIONS.

CATALOG NUMBERS					COLOR	CONFIGURATION	RATING
SPECIFICATION GRADE	HOSPITAL GRADE	ISOLATED GROUND	SURGE SUPPRESSION	SURGE SUPPRESSION HG			
HBL415	HBL415H				BROWN	NEMA 5-15R 	15A 125V
HBL415I	HBL415HI		HBL415IS		IVORY		
HBL415GY	HBL415HGY				GRAY		
HBL415W	HBL415HW				WHITE		
HBL415BK					BLACK		
	HBL415HR				RED		
		IG415			ORANGE		
			HBL415S		BLUE		
HBL420	HBL420H				BROWN	NEMA 5-20R 	20A 125V
HBL420I	HBL420HI		HBL420IS	HBL420HS	IVORY		
HBL420GY	HBL420HGY				GRAY		
HBL420W	HBL420HW				WHITE		
HBL420BK					BLACK		
	HBL420HR			HBL420HRS	RED		
		IG420			ORANGE		
			HBL420S	HBL420HS	BLUE		

CODE 74545

TOLERANCES UNLESS OTHERWISE SPECIFIED		WIRING DEVICE—KELLEMS HUBBELL INCORPORATED BRIDGEPORT, CT	
FRACTIONS	±1/64	DR. BY	AJL
DECIMALS	±.005	TR. BY	JMN
ANGLES	±2°	APP. BY	DJP
		SCALE	NONE
		CHK'D BY	DJP
		DATE	2/2/07