



M-99611



MALE LINKOSITY CONNECTOR



SLOTS ACCEPT 1/4" SCREWS
3/16" FREE PLAY IN SLOTS

TYPE II CROSS RECESS

OPTIONAL FEMALE PASS THRU WITH CAP & LABEL

- NOTES:
1. DIMENSIONS ARE IN INCHES & [MM].
 2. ALL DEVICES ARE CULUS LISTED.
 3. ENCLOSURE RATING: TYPE 4X.
 4. LINKOSITY™ IS A TRADEMARK OF LOCKHEED MARTIN.


STYLE ¹	
DIGIT	DESC.
4L	LINKOSITY

TYPE ²		NO. OF POLES ³
DIGIT	DESC.	DIGIT
20	20 AMP	02
		03
		04
		05
23	20 AMP SNIG	03
		04
		05
		06
30	30 AMP	04

CONDUCTOR COLORS ⁴	
DIGIT	DESC.
PA	GREEN/YELLOW BLACK ALL OTHERS
PB	GREEN/YELLOW/WHITE BLACK ALL OTHERS

PASS THRU ⁵	
DIGIT	DESC.
P	PASS THRU
0	NO PASS THRU

CATALOG NUMBER



LIST OF PARTS		
DESCRIPTION	MATERIAL	FINISH
ALL EXTERNAL PLASTIC PARTS	UV STABILIZED POLYESTER/POLYCARBONATE BLEND	
ALL EXTERNAL SCREWS AND HARDWARE	STAINLESS STEEL	

1	RELEASED PER DCN#12718	WRV	11/9/05
SYM	REVISIONS	APP	DATE

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE
LINKOSITY PSDA (DIST. BOX VERSIONS)

TOLERANCES UNLESS OTHERWISE SPECIFIED	WIRING DEVICE-KELLEMS HUBBELL INCORPORATED BRIDGEPORT, CT	
FRACTIONS ± 1/64	DR. BY WRV	APP. BY TLS
DECIMALS ± .005	TR. BY	SCALE 1:1
ANGLES ± 2°	CHK'D BY	DATE 07/05

DIMENSION SHEET FOR CAT. NO. REPAIRABLE NON-REPAIRABLE B M-99611 1