



M-8345

1

WIRE	COLOR
1	BROWN
2	WHITE
3	BLUE
4	BLACK
5	GRAY

LENGTH
SEE NOTE 1

1. PLUG ASSEMBLIES AVAILABLE IN 2, 4 AND 5 METER LENGTHS. CONSULT FACTORY FOR OTHER ADDITIONAL LENGTHS.
2. ONE DIGIT SUFFIX IN CATALOG NUMBER DENOTES LENGTH OF PLUG ASSEMBLY IN METERS. MCNS1512 IS 2 METERS LONG.
3. CATALOG NUMBER PREFIX MCNA - - - DENOTES A BLACK NYLON COUPLING NUT; MCMA - - - DENOTES A NICKEL PLATED BRASS COUPLING NUT;

CATALOG NUMBER SEE NOTE 3	AMPS	VOLTS	CABLE JACKET Ø
MC_S151_	4	300 VDC	0.262

LIST OF PARTS

DESCRIPTION	MATERIAL	FINISH
COUPLING NUT	SEE NOTE 3	
INSULATOR	NYLON	WHITE
"O" RING	RUBBER	BLACK
"O" RING	SILICONE	GREEN
SOCKET CONTACT	COPPER ALLOY	GOLD OVER Pd/Ni
OVERMOLD	POLYURETHANE	BLACK
CABLE	22AWG PVC	BLACK

DIMENSION SHEET FOR CAT. NO.
SEE TABLEREPAIRABLE ☐ NON-REPAIRABLE ☒

B

M-8345

1

1	10/12/00 RELEASED PER DCN8072 GPH <i>B.H.</i>	GPH	10/12/00
SYM	REVISIONS	APP	DATE

THE DESIGN AND DIMENSIONS OF THE
PRODUCT SHOWN ON THIS DRAWING ARE
SUBJECT TO CHANGE WITHOUT NOTICE

TITLE
90° FEMALE PLUG,
300VDC, 5 POLE SINGLE KEY,
INTERNAL THREAD

TOLERANCES UNLESS
OTHERWISE SPECIFIED
FRACTIONS $\pm 1/64$
DECIMALS $\pm .005$
ANGLES $\pm 2^\circ$

WIRING DEVICE-KELLEMS
HUBBELL INCORPORATED
BRIDGEPORT, CT

DR. BY GPH APP. BY *B.H.*
TR. BY SCALE NONE
CHK'D BY *B.H.* DATE 9/27/00