

M-79913




FIGURE 2

WIRE	COLOR
1	BROWN
2	WHITE
3	BLUE
4	BLACK



FIGURE 1

WIRE	COLOR
1	BROWN
2	NOT USED
3	BLUE
4	BLACK



NOTES:

1. PLUG ASSEMBLIES AVAILABLE IN 2, 4, AND 5 METER LENGTHS. CONSULT FACTORY FOR OTHER ADDITIONAL LENGTHS.
2. ONE DIGIT SUFFIX IN CATALOG NUMBER DENOTES LENGTH OF PLUG ASSEMBLY IN METERS. ME_S1312 IS 2 METERS LONG.
3. CATALOG NUMBER PREFIX MENS___ DENOTES A BLACK NYLON COUPLING NUT; MEMS___ DENOTES A NICKEL PLATED BRASS COUPLING NUT.
4. CATALOG NUMBER ME_S131_ DENOTES A 22 AWG BLACK PVC CABLE; ME_S132_ DENOTES A 18 AWG BLACK TPE CABLE.
5. ALL FIGURES ARE SHOWN WITH FEMALE PLUGS.

CATALOG NUMBER SEE NOTES 3 & 4	SEE FIGURE NUMBER	NUMBER OF POLES	AMPS	CABLE JACKET DIA.
ME_S131_	1	3	5	.209
ME_S132_			8	.240
ME_S141_	2	4	4	.224
ME_S142_			6	.259

LIST OF PARTS

DESCRIPTION	MATERIAL	FINISH
COUPLING NUT	SEE NOTE 3	3
INSULATOR, SOCKET	NYLON	WHITE
INSULATOR, PIN	NYLON	WHITE
O-RING	RUBBER	BLACK
O-RING	SILICONE	GREEN
SOCKET CONTACT	COPPER ALLOY	GOLD OVER Pd/Ni
PIN CONTACT	BRASS	GOLD OVER Pd/Ni
OVERMOLD	POLYURETHANE	BLACK
CABLE	SEE NOTE 4	4

SYM	REVISIONS	APP	DATE
3	CHANGED PER DCN7403. DJH		01/27/00 S.P.H.
2	CHANGED CURRENT RATING ON 3 AND 4 POLE PER DCN7275. DJH		11/18/99
1	RELEASED PER DCN5711-20. DJH		06/02/99

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE
STRAIGHT MALE/FEMALE, 300VDC
SINGLE KEY, EXTENSION PLUG

TOLERANCES UNLESS OTHERWISE SPECIFIED	WIRING DEVICE-KELLEMS HUBBELL INCORPORATED BRIDGEPORT, CT	
FRACTIONS ± 1/64	DR. BY DJH	APP. BY GH
DECIMALS ± .005	TR. BY	SCALE NONE
ANGLES ± 2°	CHK'D BY GH	DATE 06/02/99