



M-9472

1



10 POLE
(FEMALE FACE
SHOWN)



9 POLE
(FEMALE FACE
SHOWN)

FEMALE PLUG

MALE PLUG

9 POLE
(MALE FACE
SHOWN)

CATALOG NUMBER	NUMBER OF POLES	POSITION NUMBER	COLOR	CONDUCTOR MARKING
PH1009PEXXX	9	1	BLUE/BROWN	P1
		2	BLUE/BLACK	P2
		3	BLUE/WHITE	P3
		4	BLUE/RED	P4
		5	BLUE/GREEN	P5
		6	BLUE/VIOLET	P6
		7	BLUE/GRAY	P7
		8	BLUE/PINK	P8
		9	BLUE/TAN	P9
PH1010PEXXX	10	1	BLUE/BROWN	P1
		2	BLUE/BLACK	P2
		3	BLUE/WHITE	P3
		4	BLUE/RED	P4
		5	BLUE/GREEN	P5
		6	BLUE/VIOLET	P6
		7	BLUE/GRAY	P7
		8	BLUE/PINK	P8
		9	BLUE/TAN	P9
		10	BLUE	P10

- NOTES: UNLESS OTHERWISE SPECIFIED
- DIMENSIONS ARE IN INCHES [MM].
 - ALL DEVICES ARE 10A. 600V.
 - ALL DEVICES ARE U.L. LISTED AND ARE NOT FOR CURRENT RUPTURE.
 - THE "XXX" IN CATALOG NUMBER DENOTES LENGTH OF WIRE IN FEET. PH1009PE 050 IS FIFTY FEET LONG.

LINKOSITY™ IS A TRADEMARK OF LOCKHEED MARTIN

LIST OF PARTS

DESCRIPTION	MATERIAL	FINISH
COUPLING NUT	BRASS	NICKEL
INSULATOR, SOCKET	NYLON	WHITE
RETAINERS	NYLON	WHITE
O-RING	RUBBER	BLACK
O-RINGS	SILICONE	GREEN
SOCKET CONTACT	COPPER ALLOY	GOLD OVER Pd/Ni
OVERMOLD	POLYURETHANE	GRAY
CABLE	18 AWG PVC	GRAY
PIN CONTACT	BRASS	GOLD OVER Pd/Ni
INSULATOR, PIN	NYLON	WHITE

DIMENSION SHEET FOR CAT. NO. SEE TABLE

REPAIRABLE NON-REPAIRABLE

1	11/10/04	RELEASED PER DCN 11938.	GPH	11/10/04
SYM	REVISIONS	APP	DATE	

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE
LINKOSITY™ EXTENSION CABLE
18 AWG PLTC/ITC

TOLERANCES UNLESS OTHERWISE SPECIFIED	WIRING DEVICE-KELLEMS HUBBELL INCORPORATED BRIDGEPORT, CT	
FRACTIONS ± 1/64	DR. BY MJM	APP. BY GPH
DECIMALS ± .005	TR. BY	SCALE NONE
ANGLES ± 2°	CHK'D BY GPH	DATE 11/10/04

M-9472

1