


M-9622 1



FEMALE FACE

FEMALE PLUG

MALE PLUG

NOTES: UNLESS OTHERWISE SPECIFIED

1. DIMENSIONS ARE IN INCHES(MM).
2. ALL DEVICES ARE 7A, 300VAC.
3. ALL DEVICES ARE U.L. LISTED AND ARE NOT FOR CURRENT RUPTURE.
4. THE "XXX" IN CATALOG NUMBER DENOTES LENGTH OF WIRE IN FEET. PH1012PE 0 1 0 IS TEN FEET LONG.

CATALOG NUMBER	NUMBER OF POLES	POSITION NUMBER	COLOR	CONDUCTOR NUMBER
PH1012PEXXX	12	1	BLUE	P1
		2		P2
		3		P3
		4		P4
		5		P5
		6		P6
		7		P7
		8		P8
		9		P9
		10		P10
		11		P11
		12		P12

LINKOSITY™ IS A TRADEMARK OF LOCKHEED MARTIN

LIST OF PARTS

DESCRIPTION	MATERIAL	FINISH
COUPLING NUT	BRASS	NICKEL
INSULATOR, SOCKET	NYLON	WHITE
RETAINERS	NYLON	WHITE
O-RING	RUBBER	BLACK
O-RINGS	SILICONE	GREEN
SOCKET CONTACT	COPPER ALLOY	GOLD OVER Pd/Ni
OVERMOLD	POLYURETHANE	GRAY
CABLE	18 AWG PVC	GRAY
PIN CONTACT	BRASS	GOLD OVER Pd/Ni
INSULATOR, PIN	NYLON	WHITE

DIMENSION SHEET FOR CAT. NO. SEE TABLE

REPAIRABLE NON-REPAIRABLE

1	RELEASED PER DCN 12211 GH	GH	2/15/05
SYM	REVISIONS	APP	DATE

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE
LINKOSITY™ M/F EXTENSION,
18 AWG ITC/PLTC CABLE

TOLERANCES UNLESS OTHERWISE SPECIFIED	WIRING DEVICE-KELLEMS HUBBELL INCORPORATED BRIDGEPORT, CT	
FRACTIONS ± 1/64	DR. BY GPH	APP. BY G.H.
DECIMALS ± .005	TR. BY	SCALE NONE
ANGLES ± 2°	CHK'D BY G.H.	DATE 2/15/05