


M-9778 1



NOTES: UNLESS OTHERWISE SPECIFIED

1. UL LISTED (PRODUCT CATEGORY CYJV). NOT FOR CURRENT INTERRUPT, RATED 30A, 600V. CABLE - LISTED (QPOR) POWER & CONTROL TRAY CABLE, 600V TYPE TC-ER.
2. THESE DEVICES SHALL CONFORM TO LINKOSITY SPECIFICATIONS -0015, -0021.
3. THE "XXX" IN CATALOG NUMBER DENOTES LENGTH OF PLUG ASSEMBLY IN FEET. PM3004PB005 IS 5 FEET LONG. TOLERANCE ± 3.0 " UP TO 5'; ± 8.0 " FROM 5' TO 25'; ± 12.0 " GREATER THAN 25'.
4. FIGURE SHOWN IS MALE IN-LINE CORDSET.
5. DIMENSIONS ARE IN INCHES [mm].
6. LINKOSITY™ IS A TRADEMARK OF LOCKHEED MARTIN.

CATALOG NUMBER SEE NOTE 3	NUMBER OF POLES	POSITION NUMBER	COLOR	CONDUCTOR MARKING
PM3004PBXXX	4	1	BLACK	P1
		2	WHITE	P2
		3	GREEN/YELLOW	P3
		4	BLACK	P4
PM3004PAXXX	4	1	BLACK	P1
		2	BLACK	P2
		3	GREEN/YELLOW	P3
		4	BLACK	P4

LIST OF PARTS

DESCRIPTION	MATERIAL	FINISH
COUPLING NUT	BRASS	NICKEL PLATE
OVERMOLD	POLYURETHANE	GRAY
CABLE	10 AWG PVC	GRAY
PIN CONTACT	BRASS	GOLD OVER Pd/Ni
INSULATOR, PIN	NYLON	WHITE

SYM	REVISIONS	APP	DATE
1	5/04/05 RELEASED PER DCN#12330 CAC	CAC	5/04/05

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE
30A STR. MALE SINGLE ENDED CABLE
LINKOSITY™
10 AWG, TC-ER CABLE

TOLERANCES UNLESS OTHERWISE SPECIFIED	WIRING DEVICE-KELLEMS HUBBELL INCORPORATED BRIDGEPORT, CT	
FRACTIONS $\pm 1/64$	DR. BY CAC	APP. BY CAC
DECIMALS $\pm .005$	TR. BY	SCALE NONE
ANGLES $\pm 2^\circ$	CHK'D BY CAC	DATE 5/03/05

DIMENSION SHEET FOR CAT. NO. M-9778
 REPAIRABLE NON-REPAIRABLE