


M-12641

1

LIST OF PARTS


DESCRIPTION	MATERIAL	FINISH
MOLDED PLUG END	PVC	SEE TABLE
PLUG COVER	BRASS	Ni PLATED
PLUG BLADES	BRASS	Ni PLATED
CABLE JACKET	PVC	SEE TABLE

DIMENSION SHEET FOR CAT. NO. SEE TABLE



REPAIRABLE NON-REPAIRABLE

CATALOG NO.	LENGTH "L" ±18"	COLOR	POWER LED
PS6350ITW	50 FT.	WHITE	NO
PS6375IT	75 FT.	YELLOW	NO
PS6375ITW	75 FT.	WHITE	NO
PS63100IT	100 FT.	YELLOW	NO
PS63100ITW	100 FT.	WHITE	NO
PS6385ITW	85 FT.	WHITE	NO
PS6375ITLED	75 FT.	YELLOW	YES
PS63100ITLED	100 FT.	YELLOW	YES



BLADE CONFIGURATION

1	INITIAL DRAWING RELEASED. PER DCN 20621 DDL	DJP	07/15/14
REV	DESCRIPTION	APP	DATE

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE
MARINE IT POWER CABLES
50A 125/250V

TOLERANCES UNLESS OTHERWISE SPECIFIED	WIRING DEVICE-KELLEMS HUBBELL INCORPORATED SHELTON, CT	
	DR. BY DDL	APP. BY <i>DJP</i>
	TR. BY	SCALE 1:2
	CHK. BY <i>DJP</i>	DATE 07/15/14

NOTES: (UNLESS OTHERWISE SPECIFIED)

1. ALL DIMENSIONS ARE IN INCHES
[mm]

B

M-12641

1