


M-9568 1

CATALOG NUMBER	POSITION NUMBER	COLOR	CONNECTOR MARKING
RF1010PEXXX	1	BLUE	P1
	2	BLUE	P2
	3	BLUE	P3
	4	BLUE	P4
	5	BLUE	P5
	6	BLUE	P6
	7	BLUE	P7
	8	BLUE	P8
	9	BLUE	P9
	10	BLUE	P10
RF1009PEXXX	1	BLUE	P1
	2	BLUE	P2
	3	BLUE	P3
	4	BLUE	P4
	5	BLUE	P5
	6	BLUE	P6
	7	BLUE	P7
	8	BLUE	P8
	9	BLUE	P9



LIST OF PARTS

DESCRIPTION	MATERIAL	FINISH
RECEPTACLE SHELL	BRASS	NICKEL
INSULATOR	NYLON	WHITE
RETAINER	NYLON	WHITE
O-RING	RUBBER	BLACK
GASKET	POLYETHYLENE	YELLOW
SOCKET CONTACT	COPPER ALLOY	GOLD OVER Pd/Ni
LOCKNUT	STEEL	ZINC
WIRE	16 AWG PVC	SEE TABLE

DIMENSION SHEET FOR CAT. NO. SEE TABLE

REPAIRABLE  NON-REPAIRABLE

1	11/10/04 RELEASED PER DCN 11938 MJM GH	GH	11/10/04
SYM	REVISIONS	APP	DATE

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE  
FEMALE RECEPTACLE  
HEX MOUNT

TOLERANCES UNLESS OTHERWISE SPECIFIED	WIRING DEVICE-KELLEMS HUBBELL INCORPORATED BRIDGEPORT, CT	
FRACTIONS ±1/64	DR. BY MJM	APP. BY GH
DECIMALS ±.005	TR. BY	SCALE NONE
ANGLES ±2°	CHK'D BY GH	DATE 11/10/04

NOTES: (UNLESS OTHERWISE SPECIFIED)

- DIMENSIONS ARE IN INCHES [MM].
- ALL DEVICES ARE 10A. 600 VAC.
- ALL DEVICES ARE U.L. LISTED AND ARE NOT FOR CURRENT RUPTURE.
- THE "XXX" IN CATALOG NUMBER DENOTES LENGTH OF WIRE IN FEET. PH1009PE 0 5 0 IS FIFTY FEET LONG.

M-9568 1