

M-9413

5




FIGURE 1

WIRE	COLOR
1	BLACK
2	WHITE
3	GREEN/YELLOW
4	BLACK
5	BLACK




FIGURE 2

WIRE	COLOR
1	BLACK
2	BLACK
3	GREEN/YELLOW
4	BLACK




FIGURE 3

WIRE	COLOR
1	BLACK
2	WHITE
3	GREEN/YELLOW
4	BLACK




FIGURE 4

WIRE	COLOR
1	BLACK
2	WHITE
3	GREEN/YELLOW




FIGURE 5

WIRE	COLOR
1	BLUE
2	BLUE




FIGURE 6

WIRE	COLOR
1	BLACK
2	BLACK
3	GREEN/YELLOW
4	BLACK
5	BLACK




FIGURE 7

WIRE	COLOR
1	BLACK
2	BLACK
3	GREEN/YELLOW





FIGURE 8

WIRE	COLOR
1	BLACK
2	BLACK
3	GREEN/YELLOW
4	BLACK



NOTES UNLESS OTHERWISE SPECIFIED:

- 1) UL LISTED (PRODUCT CATEGORY CYJV) NOT FOR CURRENT INTERRUPT RATING 20A/600VAC. WIRE - LISTED TYPE MTW.
- 2) DIMENSIONS ARE IN INCHES [mm].
- 3) THESE DEVICES SHALL CONFORM TO LINKOSITY SPECIFICATIONS -0015, -0177.
- 4) LINKOSITY™ IS A TRADEMARK OF LOCKHEED MARTIN.

CODE 74545

LIST OF PARTS

DESCRIPTION	MATERIAL	FINISH
RECEPTACLE SHELL	BRASS	NICKEL
INSULATOR	NYLON	WHITE
LOCKNUT	STEEL	ZINC
O-RING	RUBBER	BLACK
O-RING	RUBBER	BLACK
SOCKET CONTACT	COPPER ALLOY	GOLD OVER Pd/Ni
WIRE 12 AWG	COPPER	STRANDS

DIMENSION SHEET FOR CAT. NO.
SEE TABLEREPAIRABLE ☐NON-REPAIRABLE ☒

B

M-9413

5

THE DESIGN AND DIMENSIONS OF THE
PRODUCT SHOWN ON THIS DRAWING ARE
SUBJECT TO CHANGE WITHOUT NOTICE

TITLE

20A FEMALE RECEPTACLE
LINKOSITY™
HEX MOUNT, 600VTOLERANCES UNLESS
OTHERWISE SPECIFIED
FRACTIONS : 1/8"
DECIMALS : .005
ANGLES : 2°WIRING DEVICE-KELLEWS
HUBCELL INCORPORATED
BRIDGEPORT, CTDR. BY MJM APP. BY RDK
TR. BY SCALE NONE
CHK'D BY RDK DATE 7/19/04

CATALOG NUMBERS (XXX INDICATES LENGTH)	SEE FIGURE NUMBER	NUMBER OF POLES
RF2005PBXXX	1	5
RF2004PAXXX	2	4
RF2004PBXXX	3	4
RF2003PBXXX	4	3
RF2002PBXXX	5	2
RF2005PAXXX	6	5
RF2003PAXXX	7	3
RF2004PAXXXM1	8	4