


M-9427 2



NOTES: UNLESS OTHERWISE SPECIFIED

1. UL LISTED (PRODUCT CATEGORY CYJV). NOT FOR CURRENT INTERRUPT, RATED 30A, 600V.
WIRE - LISTED TYPE (MTW).
2. DIMENSIONS ARE IN INCHES [mm].
3. THESE DEVICES SHALL CONFORM TO LINKOSITY SPECIFICATIONS -0015, -0021.
4. LINKOSITY™ IS A TRADEMARK OF LOCKHEED MARTIN.

CATALOG NO. (XXX INDICATES LENGTH)	FIGURE NO.	WIRE NO.	COLOR	NUMBER OF POLES	AMPS
RF3004PAXXX	1	1	BLACK	4	30
		2	BLACK		
		3	GREEN/YELLOW		
		4	BLACK		
RF3004PBXXX	2	1	BLACK	4	30
		2	WHITE		
		3	GREEN/YELLOW		
		4	BLACK		

LIST OF PARTS

DESCRIPTION	MATERIAL	FINISH
RECEPTACLE SHELL	BRASS	NICKEL PLATE
INSULATOR	NYLON	WHITE
LOCKNUT	STEEL	ZINC
O-RING	RUBBER	BLACK
O-RING	RUBBER	BLACK
SOCKET CONTACT	COPPER ALLOY	GOLD OVER Pd/Ni
WIRE, 10 AWG	COPPER	STRANDS
POTTING COMPOUND		BLACK

SYM	REVISIONS	APP	DATE
2	ADDED NOTES;REVISED TABLE; REVISED DIMS TO DUAL DIMS. & ADDED TOLS.;REVISED LIST OF PARTS PER DCN #12321 RCM	CAC	4/18/05
1	8/5/04 RELEASED PER DCN#11927 MJM RDK	RDK	8/5/04

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE
30A FEMALE RECEPTACLE ASSY (4P)
LINKOSITY™
HEX MOUNT, 600V

TOLERANCES UNLESS OTHERWISE SPECIFIED	WIRING DEVICE-KELLEMS HUBBELL INCORPORATED BRIDGEPORT, CT	
FRACTIONS ± 1/64	DR. BY MJM	APP. BY RDK
DECIMALS ± .005	TR. BY	SCALE NONE
ANGLES ± 2°	CHK'D BY RDK	DATE 8/5/04

DIMENSION SHEET FOR CAT. NO. M-9427
 REPAIRABLE NON-REPAIRABLE
 SEE TABLE