



M-9578


1




3 POLE



4 POLE



2 POLE



NOTES:

1. THE "XXX" SUFFIX IN CATALOG NUMBER DENOTES LENGTH OF WIRE IN FEET. RFR303PE005 HAS 5 FEET OF WIRE.
2. LINKOSITY™ IS A TRADEMARK OF LOCKHEED MARTIN.

CATALOG NUMBER	NUMBER OF POLES	POSITION NUMBER	COLOR	CONDUCTOR MARKING	AMPS
RFR302PEXXX	2	1	NOT USED		3
		2	NOT USED		
		3	BLUE	P3	
		4	BLUE	P4	
RFR303PEXXX	3	1	NOT USED		
		2	BLUE	P2	
		3	BLUE	P3	
		4	BLUE	P4	
RFR304PEXXX	4	1	BLUE	P1	
		2	BLUE	P2	
		3	BLUE	P3	
		4	BLUE	P4	

LIST OF PARTS

DESCRIPTION	MATERIAL	FINISH
RECEPTACLE SHELL	BRASS	NICKEL
INSULATOR	NYLON	WHITE
O-RING	RUBBER	BLACK
O-RING	RUBBER	BLACK
LOCKNUT	STEEL	ZINC
SOCKET CONTACT	COPPER ALLOY	GOLD OVER Pd/Ni
WIRE	22 AWG PVC	SEE TABLE

DIMENSION SHEET FOR CAT. NO.

SEE TABLE

REPAIRABLE ☐

NON-REPAIRABLE ☒

B

M-9578

1

1	1/17/05 RELEASED PER DCN12174 GPH	GH	1/17/05
SYM	REVISIONS	APP	DATE

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE
LINKOSITY™ REVERSE KEY FEMALE RECEPTACLE

TOLERANCES UNLESS OTHERWISE SPECIFIED FRACTIONS ± 1/64 DECIMALS ± .005 ANGLES ± 2°	WIRING DEVICE-KELLEMS HUBBELL INCORPORATED BRIDGEPORT, CT	
	DR. BY GPH	APP. BY G.H.
	TR. BY	SCALE NONE
	CHK'D BY G.H.	DATE 1/17/05