




M-10665 1



CATALOG NO'S	COLOR	CONFIG	RATING
RR155	BROWN	 NEMA 6-15R	15A 250V
RR155I	IVORY		
RR155W	WHITE		
RR155GY	GRAY		
RR155BK	BLACK		
RR155AL	ALMOND		
RR155LA	LIGHT ALMOND		
RR205	BROWN	 NEMA 6-20R	20A 250V
RR205I	IVORY		
RR205W	WHITE		
RR205GY	GRAY		
RR205BK	BLACK		
RR205AL	ALMOND		
RR205LA	LIGHT ALMOND		

NOTE:  
 1) #14 AWG TO #10 AWG SOLID AND OR STRANDED COPPER WIRE ONLY  
 2) DIM'S ARE IN INCHES [MM].

CODE 74545

LIST OF PARTS

DESCRIPTION	MATERIAL	FINISH
COVER	PLASTIC	SEE TABLE
DRIVE SCREW	STEEL	ZINC
BASE	PLASTIC	YELLOW
BRIDGE	STEEL	ZINC
TERM ASSY	BRASS	
GROUNDING SPRING	SS	
SCREW	STEEL	ZINC
WASHER	PLASTIC	

1	06/4/07 RELEASED TO PRODUCTION PER DCN# 14002	FJ	6/4/07
SYM	REVISIONS	APP	DATE

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE  
 SINGLE RECEP 250V

TOLERANCES UNLESS OTHERWISE SPECIFIED FRACTIONS ±1/64 DECIMALS ±.005 ANGLES ±2°	WIRING DEVICE-KELLEMS HUBBELL INCORPORATED BRIDGEPORT, CT.	
	DR. BY FJ	APP. BY RK
	TR. BY	SCALE 1:1
	CHK'D BY RK	DATE 6/4/07

DIMENSION SHEET FOR CAT. NO. SEE TABLE REPAIRABLE  NON-REPAIRABLE  B M-10665 1