


M-11623 1







CATALOG NO.	RATING/TYPE	COLOR
RSD215	DP 20A DECO SWITCH,	BROWN
RSD215I	DP 20A DECO SWITCH,	IVORY
RSD215GY	DP 20A DECO SWITCH,	GRAY
RSD215W	DP 20A DECO SWITCH,	WHITE
RSD215BK	DP 20A DECO SWITCH,	BLACK
RSD215AL	DP 20A DECO SWITCH,	ALMOND
RSD215LA	DP 20A DECO SWITCH,	LT ALMOND
RSD415	4-WAY 20A DECO SWITCH,	BROWN
RSD415I	4-WAY 20A DECO SWITCH,	IVORY
RSD415GY	4-WAY 20A DECO SWITCH,	GRAY
RSD415W	4-WAY 20A DECO SWITCH,	WHITE
RSD415BK	4-WAY 20A DECO SWITCH,	BLACK
RSD415AL	4-WAY 20A DECO SWITCH,	ALMOND
RSD415LA	4-WAY 20A DECO SWITCH,	LT ALMOND

LIST OF PARTS		
DESCRIPTION	MATERIAL	FINISH
ROCKER	THERMOPLASTIC	NONE
TOP HOUSING	THERMOPLASTIC	NONE
BASE	THERMOPLASTIC	NONE
RUBBER INSERT	ELASTOMER	NONE
RUBBER BUMPER	ELASTOMER	NONE
DRIVE SCREW	STEEL	ZINC PLATED
MOUNTING SCREW	STEEL	ZINC PLATED
STRAP	STEEL	ZINC PLATED
SPRING	STEEL	NONE
STAPLE	STEEL	NONE
BRUSH	BRASS ALLOY	BRIGHT DIP
SILVER CONTACT	SILVER ALLOY	NONE
COMMON TERMINAL	BRASS ALLOY	SILVER PLATED
SP STATIONARY TERM.	BRASS ALLOY	BRIGHT DIP
GROUND TERMINAL	BRASS ALLOY	BRIGHT DIP
3W STATIONARY TERM.	BRASS ALLOY	BRIGHT DIP
PVC WASHER	PVC PLASTIC	NONE
BRUSH ACTUATOR	STEEL	ZINC PLATED
LAMP-WIRE PIN	BRASS ALLOY	NONE
LED LAMP		NONE

DIMENSION SHEET FOR CAT. NO. SEE CHART REPAIRABLE NON-REPAIRABLE B M-11623 1

DOUBLE POLE

4-WAY



NOTE:
 1. BASE COLOR: BLACK
 2. ALL DIMENSIONS ARE IN INCHES AND (MILLIMETERS)

1	RELEASE FOR PRODUCTION PER DCN16799	G.Z	06/30/10
SYM	REVISIONS	APP	DATE

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE
 RESIDENTIAL GRADE
 15A & 20A SNAP DECO SWITCH

TOLERANCES UNLESS OTHERWISE SPECIFIED	WIRING DEVICE-KELLEMS HUBBELL INCORPORATED BRIDGEPORT, CT		
FRACTIONS ± 1/64	DR. BY SRE	APP. BY	<i>h</i>
DECIMALS ± .005	TR. BY	SCALE	
ANGLES ± 2'	CHK'D BY <i>h</i>	DATE	7/19/10