

S1R8PTFITX

NOTES:


1. S1R8PT SUB-PLATES SUPPLIED WITH PRE WIRED , MOLDED , FOUR POSITION 20A, 125V BLACK RECEPTACLES.
2. FOLLOW MANUFACTURERS DIRECTIONS AND GUIDELINES FOR THE INSTALLATION AND MOUNTING OF THE POKE THRU AND ALL OF THE ASSOCIATED COMPONENTS.
3. FITX REPRESENTS FIT1,FIT2 OR FIT3 BASED ON REPLACEMENT FITTING BOX.
4. INCLUDES FLANGE AND UNIVERSAL COVER ASSEMBLY (S1R8CVRxx).
5. xx INDICATES FINISH OPTIONS. (BRUSHED ALUMINUM, BLACK POWDER COAT, BRASS , BRONZE , NICKEL PLATED)

REV	DESCRIPTION	APP	DATE
-----	-------------	-----	------



THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE
8" RECESSED POKE-THROUGH


TOLERANCES UNLESS OTHERWISE SPECIFIED .XX = ± .01 .XXX = ± .005 ANGLES = ± 2'	WIRING DEVICE-KELLEMS HUBBELL INCORPORATED SHELTON, CT	
	DR. BY	APP. BY
	TR. BY	SCALE
	CHK. BY	DATE



CATALOG NUMBER- S1R8PTFIT*



SECTION A-A
SCALE .15



CENTER SUB-PLATES WITH OUTER SUB PLATES

NOTES:

1. SUB PLATES INCLUDES CENTER SUB-PLATES WITH OUTER SUB-PLATES.
2. CENTER PLATE CONFIGURATIONS ALLOWS FOR 3 DUPLEXES OR UPTO 18DATA/AV JACKS. OTHER COMBINATION POSSIBLE.
3. OUTER PLATE CONFIGURATIONS AVAILABLE IN PRE-WIRED DUPLEXES OR OPENINGS TO ACCOMMODATE THIRD PARTY AV DEVICES.


REV	DESCRIPTION	APP	DATE

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE


TITLE
8" RECESSED POKE-THROUGH

TOLERANCES UNLESS OTHERWISE SPECIFIED		WIRING DEVICE-KELLEMS HUBBELL INCORPORATED SHELTON, CT	
.XX = ± .01	DR. BY	APP. BY	
.XXX = ± .005	TR. BY	SCALE	
ANGLES = ± 2'	CHK. BY	DATE	


BOTTOM JUNCTION BOXES




S1R8JNC1
1" & 1-1/2" EMT




S1R8JNC7
3/4" & (2) 1" EMT




S1R8JNC2
(2) 1" EMT




S1R8JNC8
3/4" & 1-1/4" EMT




S1R8JNC3
2" EMT




S1R8JNC9
3/4" & (2) 1-1/4" EMT




S1R8JNC4
(3) 1" EMT




S1R8JNC10
2" & 1-1/4" EMT




S1R8JNC5
1-1/2" & 1-1/4" EMT



S1R8JNC11
2" & 1-1/2" EMT



S1R8JNC6
(2) 1-1/4" EMT





S1R8JNC12
(3) 1-1/4" EMT

- NOTE:**
1. ALL DIMENSIONS ARE COMMON TO ALL CATALOG NUMBERS. BOTTOM FEED BOXES VARY AS SPECIFIED.
 2. (2) MOUNTING SCREWS SHIPPED LOOSELY (NOT SHOWN).



THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE
8" RECESSED POKE-THROUGH



TOLERANCES UNLESS OTHERWISE SPECIFIED .XX = ± .01 .XXX = ± .005 ANGLES = ± 2'	WIRING DEVICE-KELLEMS HUBBELL INCORPORATED SHELTON, CT	
	DR. BY	APP. BY
	TR. BY	SCALE
	CHK. BY	DATE





S1R8CSPA





S1R8CSPL



S1R8CSPM





S1R8CSPEXT





S1R8CSPN



CENTER SUB-PLATES - TWO AND THREE GANG





S1R8PSPU





S1R8PSPW





S1R8PSPY



S1R8PSPV



S1R8PSPX



S1R8PSPZ



OUTER SUB-PLATES

FRPT ASSEMBLY 8 INCH SUBPLATE REQUIRED FOR ALL APPLICATIONS, SOLD SEPARATELY



THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE
8" RECESSED POKE-THROUGH



TOLERANCES UNLESS OTHERWISE SPECIFIED .XX = ± .01 .XXX = ± .005 ANGLES = ± 2'	WIRING DEVICE-KELLEMS HUBBELL INCORPORATED SHELTON, CT	
	DR. BY	APP. BY
	TR. BY	SCALE
	CHK. BY	DATE





S1R8CSPB





S1R8CSPD





S1R8CSPG





S1R8CSPJ





S1R8CSPC



S1R8CSPE



S1R8CSPI



S1R8CSPK

CENTER SUB-PLATES - SINGLE GANG

NOTE:

1. RECTANGULAR SUB PLATES ARE FOR CENTER COMPARTMENT , CRESCENT SUB PLATES ARE FOR OUTER COMPARTMENTS AND ARE NOT INTER-CHANGEABLE.

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE
8" RECESSED POKE-THROUGH

TOLERANCES UNLESS OTHERWISE SPECIFIED .XX = ± .01 .XXX = ± .005 ANGLES = ± 2'	WIRING DEVICE-KELLEMS HUBBELL INCORPORATED SHELTON, CT	
	DR. BY	APP. BY
	TR. BY	SCALE
	CHK. BY	DATE