

M-12326

2

LIST OF PARTS

DESCRIPTION	MATERIAL	FINISH
TOP	NYLON 6/6	SPI A-3
BASE	NYLON 6/6	SPI A-3
LINE CONTACTS	BRASS	
GROUND CONTACT	BRASS	
BRIDGE	.04 GALV STL	
STAPLE	S.S.	
WASHER	PVC FILM	BLACK
MOUNTING SCREWS	STEEL	ZINC PLT
WIRE LEAD, PRE-STRIPPED, RED, 12 AWG, 8" LENGTH		

DIMENSION SHEET FOR CAT. NO.

REPAIRABLE

☐




NON-REPAIRABLE

☐

B

M-12326

2



RATING	BROWN	IVORY	GRAY	WHITE	BLACK	ALMOND	LIGHT ALMOND	OFFICE WHITE	ORANGE	RED	BLUE
15A	SNAP5262SC	SNAP5262ISC	SNAP5262GYSC	SNAP5262WSC	SNAP5262BKSC	SNAP5262ALSC	SNAP5262LASC	--	--	SNAP5262RSC	SNAP5262BLSC
20A	SNAP5362SC	SNAP5362ISC	SNAP5362GYSC	SNAP5362WSC	SNAP5362BKSC	SNAP5362ALSC	SNAP5362LASC	--	--	SNAP5362RSC	SNAP5362BLSC

NOTES:

1. DIMENSIONS ARE IN INCHES [MM].
2. ALL DEVICES UL LISTED AND CSA CERTIFIED.

CODE 74545

2	UPDATED PER DCN19103 EB	TLS T.L.S.	10/17/12
1	RELEASED PER DCN19066 EB	TLS	
SYM	DESCRIPTION	APPROV	DATE

THE DESIGN AND DIMENSIONS OF THE
PRODUCT SHOWN ON THIS DRAWING ARE
SUBJECT TO CHANGE WITHOUT NOTICE

TITLE

DUPLEX RECEPTACLE, 15/20A 125V
SC, NON TR

TOLERANCES UNLESS
OTHERWISE SPECIFIED

FRACTIONS ±1/64
DECIMALS ±.005
ANGLES ±2°

WIRING DEVICE-KELLEMS
HUBBELL INCORPORATED
SHELTON, CT

DR. BY ebazayev APP. BY
TR. BY SCALE 1:1
CHK'D BY DATE 9/6/2012