


M12461 2



CATALOG NO:	DESCRIPTION:	COLOR:	RATING
SNAP15USB	USB CHARGER SNAP CONNECT 15A DUP RCPT	BROWN	15A 125V
SNAP15USBI	USB CHARGER SNAP CONNECT 15A DUP RCPT	IVORY	15A 125V
SNAP15USBW	USB CHARGER SNAP CONNECT 15A DUP RCPT	WHITE	15A 125V
SNAP15USBLA	USB CHARGER SNAP CONNECT 15A DUP RCPT	LIGHT ALMOND	15A 125V
SNAP15USBGY	USB CHARGER SNAP CONNECT 15A DUP RCPT	GRAY	15A 125V
SNAP15USBBK	USB CHARGER SNAP CONNECT 15A DUP RCPT	BLACK	15A 125V
SNAP20USB	USB CHARGER SNAP CONNECT 20A DUP RCPT	BROWN	20A 125V
SNAP20USBI	USB CHARGER SNAP CONNECT 20A DUP RCPT	IVORY	20A 125V
SNAP20USBW	USB CHARGER SNAP CONNECT 20A DUP RCPT	WHITE	20A 125V
SNAP20USBLA	USB CHARGER SNAP CONNECT 20A DUP RCPT	LIGHT ALMOND	20A 125V
SNAP20USBGY	USB CHARGER SNAP CONNECT 20A DUP RCPT	GRAY	20A 125V
SNAP20USBBK	USB CHARGER SNAP CONNECT 20A DUP RCPT	BLACK	20A 125V
SNAP8200USB	USB CHARGER SNAP CONNECT 15A HG DUP RCPT	BROWN	15A 125V
SNAP8200USBI	USB CHARGER SNAP CONNECT 15A HG DUP RCPT	IVORY	15A 125V
SNAP8200USBW	USB CHARGER SNAP CONNECT 15A HG DUP RCPT	WHITE	15A 125V
SNAP8200USBLA	USB CHARGER SNAP CONNECT 15A HG DUP RCPT	LIGHT ALMOND	15A 125V
SNAP8200USBGY	USB CHARGER SNAP CONNECT 15A HG DUP RCPT	GRAY	15A 125V
SNAP8200USBBK	USB CHARGER SNAP CONNECT 15A HG DUP RCPT	BLACK	15A 125V
SNAP8200USBR	USB CHARGER SNAP CONNECT 15A HG DUP RCPT	RED	15A 125V
SNAP8300USB	USB CHARGER SNAP CONNECT 20A HG DUP RCPT	BROWN	20A 125V
SNAP8300USBI	USB CHARGER SNAP CONNECT 20A HG DUP RCPT	IVORY	20A 125V
SNAP8300USBW	USB CHARGER SNAP CONNECT 20A HG DUP RCPT	WHITE	20A 125V
SNAP8300USBLA	USB CHARGER SNAP CONNECT 20A HG DUP RCPT	LIGHT ALMOND	20A 125V
SNAP8300USBGY	USB CHARGER SNAP CONNECT 20A HG DUP RCPT	GRAY	20A 125V
SNAP8300USBBK	USB CHARGER SNAP CONNECT 20A HG DUP RCPT	BLACK	20A 125V
SNAP8300USBR	USB CHARGER SNAP CONNECT 20A HG DUP RCPT	RED	20A 125V

NOTE:
 1. BASE COLOR: BLACK; COVER COLOR SEE TABLE PER CATALOG.
 2. RATING/TYPE:
 RECEPTACLE: SEE TABLE.
 USB CHARGER PORT OUTPUT: 5VDC 3A MAX.
 3. FOR CONNECTION USE WITH CAT.# SNAP1RA, SNAP2RA, SNAP1RNA, SANP2RNA, QT1RA OR QT2RA
 4. ALL DIMENSIONS ARE IN INCHES [mm].

LIST OF PARTS		
DESCRIPTION	MATERIAL	FINISH
COVER	THERMOPLASTIC	
BASE	THERMOPLASTIC	
MIDDLE HOUSING	THERMOPLASTIC	
SHUTTER	THERMOPLASTIC	
STRAP	GALVANIZED STEEL	
MOUNTING SCREW	STEEL	ZINC PLATED
WASHER	THERMOPLASTIC	
GR SPRING WIRE	STAINLESS STEEL	
GR TERMINAL	BRASS	
MAIN TERMINAL	COPPER ALLOY	
SNAP CONTACTS	COPPER ALLOY	SILVER PLATED
USB PORT	STAINLESS STEEL	

2	NO DWG CHANGE, UPDATE MODEL PER DCN #21553	<i>SV</i>	07/09/15
1	NEW RELEASE PER DCN #20169		2013.8.2
REV	DESCRIPTION	APP	DATE

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE
 SNAPCONNECT USB RECEPTACLE

TOLERANCES UNLESS OTHERWISE SPECIFIED		WIRING DEVICE-KELLEMS HUBBELL INCORPORATED SHELTON, CT	
.xx = ± .01	.xxx = ± .005	DR. BY V.C	APP. BY SM
ANGLES = ± 2°		TR. BY DL	SCALE 1:2
		CHK. BY C.Z	DATE 2013.8.2

CODE 74545

DIMENSION SHEET FOR CAT. NO. M12461
 REPAIRABLE NON-REPAIRABLE
 SEE TABLE
 B
 2