


M-12313

3



LIST OF PARTS		
DESCRIPTION	MATERIAL	FINISH
TOP	NYLON 6/6	SPI A-3
BASE	NYLON 6/6	SPI A-3
LINE CONTACTS	BRASS	
GROUND CONTACT	BRASS	
BRIDGE	.04 GALV STL	
STAPLE	S.S.	
WASHER	PVC FILM	BLACK
MOUNTING SCREWS	STEEL	ZINC PLT

REPAIRABLE NON-REPAIRABLE

3	01/17/2013 UPDATED FOR NEW LOCATION OF HG "DOT" PER DCN19283 EB	TLS <i>TLS</i>	
---	---	-------------------	--

RATING	BROWN	IVORY	GRAY	WHITE	BLACK	ALMOND	LIGHT ALMOND	OFFICE WHITE	ORANGE	RED	BLUE
15A	SNAP8200LTR	SNAP8200ILTR	SNAP8200GYLTR	SNAP8200WLTR	SNAP8200BKLTR	SNAP8200ALLTR	SNAP8200LALTR	--	--	SNAP8200RLTR	--
20A	SNAP8300LTR	SNAP8300ILTR	SNAP8300GYLTR	SNAP8300WLTR	SNAP8300BKLTR	SNAP8300ALLTR	SNAP8300LALTR	--	--	SNAP8300RLTR	--

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE
 DUPLEX RECEPTACLE, 15/20A 125V
 NON IG, TR & LED, HG

NOTES:
 1. DIMENSIONS ARE IN INCHES [MM].
 2. ALL DEVICES UL LISTED AND CSA CERTIFIED.

TOLERANCES UNLESS OTHERWISE SPECIFIED	WIRING DEVICE-KELLEMS HUBBELL INCORPORATED SHELTON, CT	
FRACTIONS ±1/64	DR. BY <i>ebazayev</i>	APP. BY
DECIMALS ±.005	TR. BY	SCALE 1:1
ANGLES ±2'	CHK'D BY	DATE 9/4/2012

DISTRIBUTION SHEET FOR C.T. NO.

REPAIRABLE NON-REPAIRABLE

B

M-12313

3