


M-10016 1



DIMENSIONS IN INCHES [MM]

CATALOG NUMBER	PHASE	GENERAL RATING	H.P. RATINGS				TERM. MAX. CAP. & WIRE INFO.	INSUL. STRIP [IN. [MM]		TERMINAL TORQUE LB. IN. [Nm]
			120V AC	240V AC	480V AC	600V AC		SIDE WIRE	BACK WIRE	
HBL1389MQR	3 ϕ	30A 600VAC	3	7.5	15	20	#10 AWG CU ONLY	1-1/4 [32]	5/8 [16]	20 [2.4]

LIST OF PARTS		
DESCRIPTION	MATERIAL	FINISH
BOX FRAME	STEEL	GALVANIZED
GROUND SCREW	STEEL	GREEN
SWITCH ASSY	30A DISC.	2-POLE OR 3-POLE
SW. MTG SCREW (2)	STEEL	ZINC PLATE
BOX COVER	THERMOPLASTIC	BLACK
COVER MTG. SCREW (2)	STEEL	NICKEL PLATE
LINKOSITY RECEP. FEMALE		

INITIAL RELEASE DCN#12883	WRV	1/06
SYN	REVISIONS	APP DATE

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE MOTORQUICK LINKOSITY NEMA 1 SWITCH POWER IN ONLY

TOLERANCES UNLESS OTHERWISE SPECIFIED FRACTIONS $\pm 1/84$ DECIMALS $\pm .005$ ANGLES $\pm 2^\circ$	WIRING DEVICE-KELLEMS HUBBELL INCORPORATED BRIDGEPORT, CT	
	DR. BY WRV	APP. BY
	TR. BY	SCALE 1:2
	CHK'D BY	DATE 1/06

DIMENSION SHEET FOR CAT. NO. REPAIRABLE NON-REPAIRABLE B M-10016 1