


M-10022 2



30A 600V A.C. RATINGS	
HP	VOLTAGE
1	120V AC 1 ∅
3	200-240V AC 1 ∅
5	480V AC 1 ∅
7.5	200-240V AC 3 ∅
15	480V AC 3 ∅
15	600V AC 3 ∅

DIMENSIONS IN INCHES [MM]

CATALOG NUMBER	TERM. MAX. CAP. & WIRE INFO.	TERMINAL TORQUE LB. IN. [Nm]
HBLDS3MQR	#10 AWG CU ONLY	12 [1.5]

LIST OF PARTS		
DESCRIPTION	MATERIAL	FINISH
ALL EXTERNAL PLASTIC PARTS	UV STABILIZED POLYESTER/POLYCARBONATE BLEND	
FRAME	GALVANIZED STEEL	
ALL EXTERNAL SCREWS AND HARDWARE	STAINLESS STEEL	

SYM	REVISIONS	APP	DATE
2	REVISED TABLED PER DCN #13625 RCM	TLS	1/26/07
1	INITIAL RELEASE DCN #12883	WRV	2/10/06

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE MOTORQUICK LINKOSITY ENCL. TYPE 4 DISCONNECT SWITCH POWER OUT ONLY

TOLERANCES UNLESS OTHERWISE SPECIFIED
 FRACTIONS ± 1/64
 DECIMALS ± .005
 ANGLES ± 2°

WIRING DEVICE-KELLEMS HUBBELL INCORPORATED BRIDGEPORT, CT
 DR. BY WRV APP. BY TLS
 TR. BY SCALE 1:2
 CHK'D BY TLS DATE 1/06

DIMENSION SHEET FOR CAT. NO. M-10022
 SEE TABLE
 REPAIRABLE NON-REPAIRABLE
 B
 M-10022
 2