


M-10023 2



30A 600V A.C. RATINGS	
HP	VOLTAGE
1	120V AC 1 Ø
3	200-240V AC 1 Ø
5	480V AC 1 Ø
7.5	200-240V AC 3 Ø
15	480V AC 3 Ø
15	600V AC 3 Ø

DIMENSIONS IN INCHES [MM]

CATALOG NUMBER	TERM. MAX. CAP. & WIRE INFO.	TERMINAL TORQUE LB. IN. [Nm]
HBLDS3MQR2	#10 AWG CU ONLY	12 [1.5]

LIST OF PARTS		
DESCRIPTION	MATERIAL	FINISH
ALL EXTERNAL PLASTIC PARTS	UV STABILIZED POLYESTER/POLYCARBONATE BLEND	
FRAME	GALVANIZED STEEL	
ALL EXTERNAL SCREWS AND HARDWARE	STAINLESS STEEL	

SYM	REVISIONS	APP	DATE
2	REVISED RATING & CATALOG TABLES PER DCN #13625 RCM	TLS	1/26/07
1	INITIAL RELEASE DCN #12883	WRV	2/10/06

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE MOTORQUICK LINKOSITY ENCL. TYPE 4 DISCONNECT SWITCH POWER IN AND POWER OUT

TOLERANCES UNLESS OTHERWISE SPECIFIED	WIRING DEVICE-KELLEMS HUBBELL INCORPORATED BRIDGEPORT, CT	
FRACTIONS ± 1/64	DR. BY WRV	APP. BY TLS
DECIMALS ± .005	TR. BY	SCALE 1:2
ANGLES ± 2°	CHK'D BY TLS	DATE 1/06

DIMENSION SHEET FOR CAT. NO. M-10023
 REPAIRABLE NON-REPAIRABLE
 SEE TABLE
 B
 M-10023
 2