


M-10024 2



30A 600V A.C. RATINGS	
HP	VOLTAGE
1	120V AC 1 ∅
3	200-2400V AC 1 ∅
5	480V AC 1 ∅
7.5	200-2400V AC 3 ∅
15	480V AC 3 ∅
15	600V AC 3 ∅

LIST OF PARTS		
DESCRIPTION	MATERIAL	FINISH
ALL EXTERNAL	UV STABILIZED	
PLASTIC PARTS	POLYESTER/ POLYCARBONATE BLEND	
FRAME	GALVANIZED STEEL	
ALL EXTERNAL SCREWS AND HARDWARE	STAINLESS STEEL	

DIMENSION SHEET FOR CAT. NO. SEE TABLE

REPAIRABLE NON-REPAIRABLE

B

M-10024

2

2	REVISED RATING & CAT. NO. TABLES PER DCN 13625 RCM	TLS	1/26/07
1	INITIAL RELEASE DCN #12883	WRV	2/10/08
SYM	REVISIONS	APP	DATE

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE MOTORQUICK LINKOSITY ENCL. TYPE 4 DISCONNECT SWITCH POWER OUT PIGTAIL

DIMENSIONS IN INCHES [MM]

CATALOG NUMBER	TERM. MAX. CAP. & WIRE INFO.	TERMINAL TORQUE LB. IN. [Nm]	LINKOSITY PIGTAIL LENGTH (FT)
HBLDS3M05	#10 AWG CU ONLY	12 [1.5]	5

TOLERANCES UNLESS OTHERWISE SPECIFIED	WIRING DEVICE-KELLEMS HUBBELL INCORPORATED BRIDGEPORT, CT	
FRACTIONS ± 1/64	DR. BY WRV	APP. BY TLS
DECIMALS ± .005	TR. BY	SCALE 1:2
ANGLES ± 2°	CHK'D BY TLS	DATE 1/06