




M-11258

3

NOTES:
(UNLESS OTHERWISE SPECIFIED)

1. DIMENSIONS ARE IN INCHES [MM]
2. BOX CAPACITY 28 CUBIC INCH [460 CUBIC CENTIMETERS].



LIST OF PARTS

DESCRIPTION	MATERIAL	FINISH
COVER ASSY	BRASS	
GASKET	NEOPRENE	
SCREWS	BRASS	
TILE FLANGE	BRASS	
RECEPT FLANGE	ALUMINUM	POWDER COAT

3	12/2/09 CHGD RECEPT FLANGE FROM D-6151201 TO D-6193901 PER EC 16200	DMP	12/2/09
2	6/9/09 REVISED TO REMOVE OUTLET BOX PER EC 15787	DMP	6/9/09
1	2/18/09 FOR PRODUCTION PER EC 15542	DMP	2/18/09
SYM	REVISIONS	APP	DATE

THE DESIGN AND DIMENSIONS OF THE
PRODUCT SHOWN ON THIS DRAWING ARE
SUBJECT TO CHANGE WITHOUT NOTICE

TITLE
WOOD FLOOR BOX
TILE/FLUSH MOUNT

TOLERANCES UNLESS
OTHERWISE SPECIFIED

FRACTIONS $\pm 1/64$
DECIMALS $\pm .005$
ANGLES $\pm 2^\circ$

HUBBELL WIRING
SYSTEMS
BRIDGEPORT, CT.

DR. BY DMP	APP. BY
TR. BY	SCALE NONE
CHK'D BY	DATE 6/13/07

CATALOG	FINISH	DESCRIPTION
RF509BR	SOLID BRUSHED BRASS	FLOOR BOX FOR TILE