


M115151



NOTES: (UNLESS OTHERWISE SPECIFIED)  
 1) ALL DIMENSIONS ARE IN INCHES [mm].  
 2) UL/c UL LISTED.  
 3) ELECTRICAL RATINGS: 15A, 125V, 1875W.  
 4) ON/OFF MASTER SWITCH WITH BUILT-IN CIRCUIT BREAKER.  
 5) HBL6PS350YL PICTURED. HBL8PS350YL VERSION HAS 8 RECEPTACLES.  
 6) UL VOLTAGE PROTECTION LEVEL: 400V. (L-N)  
 7) Inom. : 6kV, 3kA.  
 8) JOULE RATING: 350J.

LIST OF PARTS		
DESCRIPTION	MATERIAL	FINISH
BASE	PLASTIC	YELLOW

DIMENSION SHEET FOR CAT. NO. HBL6PS350YL, HBL8PS350YL REPAIRABLE  NON-REPAIRABLE

1	01/12/10 RELEASE TO PRODUCTION PER DCN 16208 DLI	SL	3-10-10	B
SYM	REVISIONS	APP	DATE	
THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE				
TITLE SPD WITH CORD MANAGEMENT				
TOLERANCES UNLESS OTHERWISE SPECIFIED		WIRING DEVICE-KELLEMS HUBBELL INCORPORATED BRIDGEPORT, CT		
FRACTIONS ±1/64	DR. BY DLI	APP. BY SL		
DECIMALS ±.005	TR. BY	SCALE 1:2		
ANGLES ±2'	CHK'D BY SL	DATE 01/12/10		

M115151  
1