


M115161



- NOTES: (UNLESS OTHERWISE SPECIFIED)
- 1) ALL DIMENSIONS ARE IN INCHES [mm].
 - 2) UL/c UL LISTED.
 - 3) ELECTRICAL RATINGS: 15A, 125V; 1875W.
 - 4) HEAVY DUTY 14 AWG POWER CORD.

LIST OF PARTS

DESCRIPTION	MATERIAL	FINISH
BASE	STEEL	WHITE

DIMENSION SHEET FOR CAT. NO.

HBL6MPS

REPAIRABLE

NON-REPAIRABLE

B

M11516

1

1	01/12/10 RELEASE TO PRODUCTION PER DCN 16208 DLI	SL	3-10-10
---	--	----	---------

SYM	REVISIONS	APP	DATE

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE
METAL HOUSING RELOCATABLE POWER TAP

TOLERANCES UNLESS OTHERWISE SPECIFIED	WIRING DEVICE--KELLEMS HUBBELL INCORPORATED BRIDGEPORT, CT	
FRACTIONS ±1/64	DR. BY DLI	APP. BY SL
DECIMALS ±.005	TR. BY	SCALE 1:2
ANGLES ±2°	CHK'D BY SL	DATE 01/12/10