


(4) 1" & 1-1/4" CONCENTRIC TRADE SIZE KNOCKOUTS, ENDS ONLY.

2" TRADE SIZE KNOCKOUT THIS LOCATION ONLY



SECTION A-A

CABLE SERVICE AREA
INTERNAL VOLUME:
290.2 CU IN.,
4755 CUBIC CM

6 GANG
INTERNAL
VOLUME:
155.7 CU IN.
2551 CUBIC CM


GROUNDING
SCREWS

3 GANG
INTERNAL
VOLUME:
83.1 CU IN.
1361 CUBIC CM

(4) LEVELING
FEET -
0 TO 2" [50]
ADJUSTMENT
FROM FLUSH
AS SHOWN

(9) 1", 1-1/4"
& 1-1/2"
CONCENTRIC
TRADE SIZE
KNOCKOUTS
MARKED "Y"

M-11559 1



NOTES:

- 1) ACCEPTS STANDARD SIZE WALL PLATES - 1, 3, & 6 GANG. SOLD SEPARATELY.
- 2) TEMPORARY COVER NOT SHOWN.
.12 [3.0] THK. X 12.5 [315.5] X 14 [355.6]
- 3) ALL DIMENSIONS ARE IN INCHES AND [MILLIMETERS]
- 4) DIVIDERS ARE REMOVABLE.

LIST OF PARTS

DESCRIPTION	MATERIAL	FINISH
FLOOR BOX	STEEL	ZINC
DIVIDER	STEEL	ZINC
MOUNTING BRACKETS	STEEL	ZINC
LEVELING FEET	STEEL	ZINC
TEMPORARY COVER (NOT SHOWN)	STEEL	ZINC
FASTENERS	STEEL	ZINC

1	RELEASED PER DCN18595	3/9/10
SYM	REVISIONS	APP DATE

THE DESIGN AND DIMENSIONS OF THE
PRODUCT SHOWN ON THIS DRAWING ARE
SUBJECT TO CHANGE WITHOUT NOTICE

TITLE
RECESSED FLOOR BOX
4 IN DEEP, 11 GANG

TOLERANCES UNLESS
OTHERWISE SPECIFIED
FRACTIONS ± 1/64
DECIMALS ± .005
ANGLES ± 2°

WIRING DEVICE-KELLEMS
HUBBELL INCORPORATED
BRIDGEPORT, CT
DR. BY SRE APP. BY
TR. BY SCALE 1:2
CHK'D BY DATE 3/9/10

DIMENSION SHEET FOR CAT. NO.
CFB1164

REPAIRABLE ☐ NON-REPAIRABLE ☒

B

M-11559

1