


M-12546 1

CORD LENGTH  
6 FEET



- NOTES: (UNLESS OTHERWISE SPECIFIED)
- 1) ALL DIMENSIONS ARE IN INCHES [mm].
  - 2) UL/c UL LISTED.
  - 3) ELECTRICAL RATINGS: 15A, 125V, 1875W.
  - 4) ON/OFF MASTER SWITCH WITH BUILT-IN CIRCUIT BREAKER.
  - 5) USB CHARGE PORTS PROVIDED
  - 6) UL VOLTAGE PROTECTION LEVEL: 400V. (L-N)
  - 7) I<sub>nom.</sub> : 6kV, 3kA.
  - 8) JOULE RATING: 1050J.

LIST OF PARTS

DESCRIPTION	MATERIAL	FINISH
HOUSING	THERMOPLASTIC	BLACK
CORD	---	BLACK

DIMENSION SHEET FOR CAT. NO. HBL4PS1050USBA  
REPAIRABLE  NON-REPAIRABLE


1	RELEASED FOR PRODUCTION PER DCN 20347. MYA 2/7	DJP	2-20-14
SYM	REVISIONS	APP	DATE

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE  
SPD WITH USB CHARGE PORTS

TOLERANCES UNLESS OTHERWISE SPECIFIED FRACTIONS ±1/64 DECIMALS ±.005 ANGLES ±2'	WIRING DEVICE-KELLEMS HUBBELL INCORPORATED SHELTON, CT	
	DR. BY MYA	APP. BY DJP
	TR. BY	SCALE
	CHK'D BY <i>DJP</i>	DATE 2/20/14

M-12546 1