


M-14218

1



NOTES:
1) DIMENSIONS ARE INCHES[MM]

WIRE FILL CAPACITY:

POWER CONDUCTORS (12 AWG THHN)		
CHANNEL SIDE (EACH)	40% FILL	SUGGESTED MAX
	8	7
DATA CONDUCTORS (0.215 DIA)		
CHANNEL SIDE (EACH)	40% FILL	SUGGESTED MAX
	3	4
CENTER	7	9
DATA CONDUCTORS (0.250 DIA)		
CHANNEL SIDE (EACH)	40% FILL	SUGGESTED MAX
	2	3
CENTER	5	6
CAGE CODE 74545		

CAT NO	DESCRIPTION	LENGTH	FINISH
HBLFMR6A	FLOOR MOUNTED RACEWAY TRACK 6', ALUMINUM	6 FT	ANODIZED
HBLFMR6DG	FLOOR MOUNTED RACEWAY TRACK 6', DARK GRAY	6 FT	POWDER COAT GRAY
HBLFMR3A	FLOOR MOUNTED RACEWAY TRACK 3', ALUMINUM	3 FT	ANODIZED
HBLFMR3DG	FLOOR MOUNTED RACEWAY TRACK 3', DARK GRAY	3 FT	POWDER COAT GRAY
HBLFMR1A	FLOOR MOUNTED RACEWAY TRACK 1', ALUMINUM	1 FT	ANODIZED
HBLFMR1DG	FLOOR MOUNTED RACEWAY TRACK 1', DARK GRAY	1 FT	POWDER COAT GRAY
HBLFMR123A	FLOOR MOUNTED RACEWAY TRACK 1'+2'+3', ALUMINUM	KIT: 1+2+3 FT	ANODIZED
HBLFMR123DG	FLOOR MOUNTED RACEWAY TRACK 1'+2'+3', DARK GRAY	KIT: 1+2+3 FT	POWDER COAT GRAY


LIST OF PARTS

DESCRIPTION	MATERIAL	FINISH
RACEWAY BASE	ALUMINUM	
RACEWAY COVER	ALUMINUM	SEE TABLE
RACEWAY EDGE	THERMOPLASTIC	
CLIPS	GALV. STEEL	
SPLICE	GALV. STEEL	
SET SCREWS	STEEL	PAINTED

1	RELEASED PER DCN# 191120105745	EMD	11/13/19
REV	DESCRIPTION	APP	DATE

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE IN INCHES [mm].

TITLE
FLOOR MOUNTED RACEWAY TRACK


WIRING DEVICE-KELLEMS HUBBELL INCORPORATED
 SHELTON, CT

TOLERANCES UNLESS OTHERWISE SPECIFIED .XX = ±.01 .XXX = ±.005 ANGLE TOL. ±2'	DR. BY EMD	SCALE 1/2
	CHK. BY	DATE 11/13/19

DIMENSION SHEET FOR CAT. NO. **M-14218** **SEE TABLE** **B** **1**