



M-2922 2



NOTES:

1. WIRE CAPACITY #10-#6 AWG, SOLID OR STRANDED COPPER WIRE ONLY.
2. IP44 SUITABILITY.
3. ALL DIMENSIONS IN INCHES.
[mm]

CODE 74545



TITLE

20A 250V.D.C. 30A 600V.A.C.
4 WIRE HUBBELLOCK ANGLE INLET

LIST OF PARTS

DESCRIPTION	MATERIAL	FINISH
BLADE HOLDER	BAKELITE	BLACK
CONTACTS	BRONZE	
GROUND SHUNT	.031 BRASS	USED ON CAT. 21447-X ONLY
PRESSURE TERMS	COPPER	
PRESSURE SCREWS	STEEL	ZINC PL.
EYELETS	.008 BRASS	
HOUSING	ALUMINUM	
FLAP	ALUMINUM	
GASKET	NEOPRENE	GRAY
SPACER	NYLON	

2	REMOVED SAME AS NOTE; ADDED NOTES 1 TO 3; CONVERTED DIMS. DECIMAL & METRIC; 3/4" N.P.T. WAS 3/4" PIPE TAP; REVISED TITLE; ADDED SPACER CALLOUT PER DCN 11902 RCM	JPP	1/20/05
1	"X" REMOVED FROM CAT. NOS.		4/11/69

SYM REVISIONS APP DATE

SUPERSEDES DWG. DATED 9-2-53.

TOLERANCES UNLESS
OTHERWISE SPECIFIED
FRACTIONS $\pm 1/64$
DECIMALS $\pm .005$
ANGLES $\pm 2^\circ$

HARVEY HUBBELL, INC.

BRIDGEPORT, CONN.

DR. BY RDT APP. BY

TR. BY SCALE FULL

CHK'D. BY DATE 12-26-67

DIMENSION SHEET FOR CAT. NO.

HBL21447

REPAIRABLE ☐ NON-REPAIRABLE ☒

B

M-2922

2