



M-4093



LIST OF PARTS

DESCRIPTION	MATERIAL	FINISH
FLANGED CASING	.062 STEEL	ALUM SPRAY
BRACKET	.062 STEEL	ZINC PL.
LIFT COVER	.062 STEEL	ZINC PL.
SPRING	.045 ST. ST.	
INSULATORS	PHENOLIC	
CONTACT BLADES	.100 BRASS	
3-TERMINALS	.070 COPPER	
RD. HD. SCREWS	STEEL	ZINC PL.
GASKETS	.002 RUBBER	
4-PRESSURE SCR.	STEEL	CADMIUM
GR. SPRING	.025 BRONZE	
GR. TERMINAL	.062 COPPER	

DIMENSION SHEET FOR CAT. NO. 3768

REPAIRABLE ☐ NON-REPAIRABLE ☒

B M-4093

1	CASING THICKNESS WAS .078	7-7-69	ASM
SYM	REVISIONS	APP	DATE

TITLE 50A 250V.D.C., 50A 600V.A.C.
3 POLE, 4 WIRE NON-INTERCHANGEABLE
TWIST-LOCK FLANGED INLET
WITH LIFT COVER.

TOLERANCES UNLESS
OTHERWISE SPECIFIED
FRACTIONS $\pm 1/64$
DECIMALS $\pm .005$
ANGLES $\pm 2^\circ$

HARVEY HUBBELL, INC.

BRIDGEPORT, CONN.

DR. BY P.H.F. APP. BY A.S.
TR. BY SCALE 1=1
CHK'D. BY J.C.H. DATE 7-9-69