



M-4436 6



3.19
[81.0]



5.44
[138.2]

1.09
[27.7]

NOTES:

1. WIRE CAPACITY: #8/5 AWG TO #4/5 AWG COPPER WIRE ONLY.
2. CORD RANGE: Ø 1.00 TO 1.45, TYPE "S" OR "SO".
[25.4] [36.8]
3. ALL DIMENSIONS TO BE INCHES.
[mm]

LIST OF PARTS

DESCRIPTION	MATERIAL	FINISH
INSULATORS	DUREZ	BLACK
BUSHING	RUBBER	
RETAINER COVER	POLY-CARBONATE	BLUE
COVER	062 STEEL	ZINC PL.
CORD CLAMPS	078 C.R.S.	YEL. NYLON COATING
CONTACT SPRINGS	040 COPPER	
GROUNDING SPRING	031 PHOS. BRZ	
GROUND CLAMP	050 C.R.S.	ZINC PL.
CLAMPS	ALUMINUM	WHITE
CLAMP SCREWS	STEEL	ZINC PL.
CENTER POST	STEEL	ZINC PL.
AUX. SPRING	020 BRONZE	
COIL SPRING	055 ST WIRE	COPPER PL.

DIMENSION SHEET FOR CAT. NO. HBL26516

REPAIRABLE NON-REPAIRABLE

6	ADDED NOTES 1 THRU 3: "HBL26516" WAS "26516"; REMOVED "RUBBER GRIP" & "CORD GRIP" CALLOUTS; CONVERTED ALL DIMS. TO DECIMAL & METRIC PER DCN 11902 RCM	JPP	1/27/05
SYM	REVISIONS	APP	DATE

B M-4436

TITLE
60A 600VAC, 4 POLE, 5 WIRE
GROUNDING HUBBELLOCK CONNECTOR

TOLERANCES UNLESS OTHERWISE SPECIFIED		HARVEY HUBBELL, INC.	
BRIDGEPORT, CONN.			
FRACTIONS ± 1/64	DR. BY <u>DJR</u>	APP. BY	
DECIMALS ± .005	TR. BY	SCALE <u>FULL</u>	
ANGLES ± 2°	CHK'D. BY	DATE <u>3-4-66</u>	