


M-4558 | 1



LIST OF PARTS		
DESCRIPTION	MATERIAL	FINISH
BODY	BAKELITE	BLACK
ANGLE CORD BASE	NYLON	BLACK
CORD CLAMP	NYLON	BLACK
NEUT. CONT. SLEEVE	BRASS	
CONT. SPR. BIND. PL.	BRASS	ICOPPER PL.
BINDING SCREWS	BRASS	ICOPPER PL.
INSULATOR	OSI FIBRE	RED

DIMENSION SHEET FOR CAT. NO. 74558

REPAIRABLE  NON-REPAIRABLE

SYMBOL	REVISIONS	APP	DATE
1	RATING REVISED WAS 15A, 250 15A, 125V 4.S.L.		3-1-79

B

M-4558

**TITLE**  
15A. 125/250V. 3 POLE 3-WIRE  
MIDGET TWIST-LOCK CORD CONNECTOR,  
WITH NYLON ANGLE CORD GRIPS.

TOLERANCES UNLESS OTHERWISE SPECIFIED		HARVEY HUBBELL, INC. BRIDGEPORT, CONN.	
FRACTIONS ± 1/64	DR. BY <u>D.J.R.</u>	APP. BY	
DECIMALS ± .005	TR. BY	SCALE <u>FULL</u>	
ANGLES ± 2°	CHK'D. BY	DATE <u>10-3-66</u>	

CODE 74545