



M-5434 1



Ø .265  
4 HOLES

NOTES:

1. WIRE CAPACITY: #6 AWG TO #2 AWG, SOLID OR STRANDED COPPER WIRE ONLY.
2. ALL DIMENSIONS TO BE INCHES.  
[mm]



LIST OF PARTS

DESCRIPTION	MATERIAL	FINISH
INSULATORS	DUREZ	BLACK
CONTACT SPRINGS	040 COPPER	
GR. SHUNT	020 BRASS	
CLAMPS	ALUMINUM	1-GREEN
CENTER POST	STEEL	ZINC PL.
AUX. SPRING	020 BRONZE	
COIL SPRING	055 ST. WIRE	COPPER PL.
CASING	025 BRASS	ZINC PL.
COVER	CAST ALUM.	GRAY

DIMENSION SHEET FOR CAT. NO. HBL25603

REPAIRABLE  NON-REPAIRABLE

1	ADDED NOTES 1 & 2; "HBL25603" WAS "25603"; CONVERTED ALL DIMENSIONS TO DECIMAL & METRIC PER DCN 11902 RCM	JPP	1/28/05
SYM	REVISIONS	APP	DATE

B M-5434

**TITLE**  
60A 250VAC, 2 POLE, 3 WIRE  
MOBILE X-RAY HUBBELLOCK OUTLET  
GROUNDED

**TOLERANCES UNLESS OTHERWISE SPECIFIED**  
FRACTIONS ± 1/64  
DECIMALS ± .005  
ANGLES ± 2°

**HARVEY HUBBELL, INC.**  
BRIDGEPORT, CONN.

DR. BY ASM APP. BY \_\_\_\_\_  
TR. BY \_\_\_\_\_ SCALE HALF  
CHK'D. BY \_\_\_\_\_ DATE 2-8-72

1