



M-5436 2



- NOTES:
1. WIRE CAPACITY: #8AWG TO #4AWG COPPER WIRE ONLY.
  2. CORD RANGE: Ø.83 TO 1.30, TYPE "S" OR "SO".  
[21.1] [33.0]
  3. ALL DIMS. TO BE INCHES.  
[mm]

LIST OF PARTS		
DESCRIPTION	MATERIAL	FINISH
INSULATOR	DUREZ	BLACK
CONTACTS	BRASS	
CLAMPS	ALUMINUM	1-GREEN
CLAMP SCREWS	STEEL	ZINC PL.
GR. SHUNT	ØØ1 BRASS	
CENTER POST	STEEL	ZINC PL.
COVER	ØØ2 STEEL	GRAY
RETAINER COVER	LEXAN	GRAY
BUSHING	RUBBER	
EPOXY KIT	(NOT SHOWN)	
REDUCERS	RUBBER	

SYM	REVISIONS	APP	DATE
2	ADDED NOTE 1 THRU 3; "HBL25615" WAS "25615"; REMOVED "RUBBER GRIP" CALLOUT; CONVERTED ALL DIMS. TO DECIMAL & METRIC; REVISED TITLE; ADDED "NOT SHOWN" TO "EPOXY KIT" IN PARTS LIST PER DCN 11902 RCM	JPP	2/5/05
1	SPEC'S. REVISED	[Signature]	9-18-73

DIMENSION SHEET FOR CAT. NO. HBL25615  
 REPAIRABLE  NON-REPAIRABLE   
**B**  
**M-5436**  
**2**

**TITLE**  
 60A 250VAC, 2 POLE, 3 WIRE  
 MOBILE X-RAY HUBBELLOCK PLUG

TOLERANCES UNLESS OTHERWISE SPECIFIED  
 FRACTIONS ± 1/64  
 DECIMALS ± .005  
 ANGLES ± 2°

**HARVEY HUBBELL, INC.**  
 BRIDGEPORT, CONN.  
 DR. BY A.S.M. APP. BY \_\_\_\_\_  
 TR. BY \_\_\_\_\_ SCALE 1=1  
 CHK'D BY \_\_\_\_\_ DATE 2-9-72