



M-5438 2



NOTES:

1. WIRE CAPACITY: #8AWG TO #4AWG COPPER WIRE ONLY.
2. CORD RANGE: Ø .83 TO 1.30, TYPE "S" OR "SO".
[21.1] [33.0]
3. ALL DIMS TO BE INCHES.
[mm]

LIST OF PARTS		
DESCRIPTION	MATERIAL	FINISH
INSULATOR	DUREZ	BLACK
CONTACTS	BRASS	
CLAMPS	ALUMINUM	1-GREEN
CLAMP SCREWS	STEEL	ZINC PL.
GR. SHUNT	.081 BRASS	
CENTER POST	STEEL	ZINC PL.
COVER	.0625STEEL	GRAY
RETAINER COVER	LEXAN	GRAY
BUSHING	RUBBER	
CORD CLAMPS	.078CRS	YELLOW NYLON COATING
REDUCERS	RUBBER	

DIMENSION SHEET FOR CAT. NO. HBL25625
 REPAIRABLE NON-REPAIRABLE
 B
 M-5438
 2

SYM	REVISIONS	APP	DATE
2	ADDED NOTE 1 THRU 3; REVISED TITLE; REMOVED "RUBBER GRIP" & "CORD CLAMP" CALLOUTS; "HBL25625" WAS "25625"; CONVERTED ALL DIMS. TO DECIMAL & METRIC PER DCN 11902 RCM	JPP	2/5/05
1	SPEC'S REVISED	slw	9-20-73

TITLE
 60A 250VAC, 2 POLE, 3 WIRE
 MOBILE X-RAY HUBBELLOCK PLUG

TOLERANCES UNLESS OTHERWISE SPECIFIED
 FRACTIONS ± 1/64
 DECIMALS ± .005
 ANGLES ± 2°

HARVEY HUBBELL, INC.
 BRIDGEPORT, CONN.

DR. BY ASM APP. BY _____
 TR. BY _____ SCALE 1=1
 CHK'D. BY _____ DATE 2-9-72