



M-5793 1



NOTES:
1. ALL DIMENSIONS TO BE IN INCHES
[mm]

LIST OF PARTS		
DESCRIPTION	MATERIAL	FINISH
OUTLET MOUNT	.062 C.R.S.	GRAY ENAMEL
RETAINER	.062 C.R.S.	ZINC PL.
SHROUD	ALUM.	
FACE PLATE	.043 ST. STL.	
DOOR	.037 ST. STL.	
ROD	.093 ST. STL.	
PLUNGER	NYLON	
CLIP	.043 ST. STL.	
COMPRESSION SPRING	.024 WIRE	CAD. PL.
BARREL	BRASS	NICKEL PL.
LEAD WIRE		1-GREEN
SCREW-RD. HD.	STEEL	ZINC PL.
SCREW-TRUSS HD.	ST. STL.	
INSULATORS	DUREZ	BLACK
CONTACT SPRINGS	.040 COP.	
GR. SHUNT	.020 BRASS	
CLAMPS	ALUM.	1-GREEN
CENTER POST	STEEL	ZINC PL.
AUX. SPRING	.020 BRONZE	
COIL SPRING	.055 ST. WIRE	COP. PL.
CASING	.025 BRASS	ZINC PL.

SYM	REVISIONS	APP	DATE
1	ADDED NOTE 1; REVISED TITLE; ADDED COPPER WIRE CALLOUT; CONVERTED ALL DIMS TO DECIMAL & METRIC; HBL25605 WAS 25605 PER DCN 11902 RCM	JPP	1/21/05

TITLE
60A 250VAC, 2 POLE, 3 WIRE
MOBILE X-RAY HUBBELLOCK
RECEPTACLE & COVER PLATE
WITH DOOR

TOLERANCES UNLESS OTHERWISE SPECIFIED		HARVEY HUBBELL, INC.	
FRACTIONS ± 1/64		BRIDGEPORT, CONN.	
DECIMALS ± .005		DR. BY <u>S.K.</u>	APP. BY _____
ANGLES ± 2°		TR. BY _____	SCALE <u>HALF</u>
		CHK'D. BY _____	DATE <u>10-3-74</u>

CODE 74545

DIMENSION SHEET FOR CAT. NO. HBL25605
 REPAIRABLE NON-REPAIRABLE
 B M-5793
 1