


M-5841

CABLE SPECIFICATIONS	
CONDUCTOR	STRANDED COPPER
INSULATION	POLYVINYL CHLORIDE (1/32")
JACKET	POLYVINYL CHLORIDE (1/32")
JACKET COLOR	CHROME YELLOW
VOLTAGE	SJTO - 300 V
TEMPERATURE	60°C
SIZE	16/3 AWG



LIST OF PARTS

DESCRIPTION	MATERIAL	FINISH

DIMENSION SHEET FOR CAT. NO. PH-6599

REPAIRABLE NON-REPAIRABLE

B
M-5841

TITLE
3 WIRE TWIST-LOCK
TELEPHONE CABLE SET

TOLERANCES UNLESS OTHERWISE SPECIFIED FRACTIONS ± 1/64 DECIMALS ± .005 ANGLES ± 2°	HARVEY HUBBELL, INC.	
	BRIDGEPORT, CONN.	
	DR. BY C. J. G.	APP. BY
	TR. BY	SCALE FULL
	CHK'D. BY	DATE 5-20-75