M-6054 | 3





CAT. NO.	CONFIGURATION	RATING	COMMENTS	HOUSING	
				MATERIAL	COLOR
HBL320B4W HBL316B4W		20 A 125 VAC		NYLON	BLUE
HBL320B6W		20 A 250 VAC		NYLON	BLUE
HBL316B6W		16 A 220-240 VAC		NYLON	BLUE

CAT. NO.	CONFIGURATION	RATING	COMMENTS	HOUSING	
				MATERIAL	COLOR
HBL320B7W		20 A 480 VDC		NYLON	RED

NOTES (UNLESS OTHERWISE SPECIFIED)
1) TOLERANCES ARE:
DECIMALS ± .03
ANGLES ± 2°
2) DIMENSIONS ARE: INCHES
[MILLIMETERS]

CODE 74545

LIST OF PARTS

DESCRIPTION	MATERIAL	FINISH
HOUSING	SEE TABLE	
GASKET	NEOPRENE	
LOCK RING	POLYESTER	
INTERIOR	THERMOSET	
PINS	BRASS	
TERMINAL SCREWS	ST. STEEL	
FLANGE	NYLON	
ASSEMBLY SCREWS	ST. STEEL	

SYM	REVISIONS	APP	DATE
4	REDRAWN ON CAD WITH CHANGES. ADDED NOTES 1 & 2, "16A" TO DWG. TITLE AND "HOUSING" AND "COMMENTS" COLUMNS TO TABLE . "Ø" WAS "DIA." AND "[XX.X]" WAS "MM". IN LIST OF PARTS, "SEE TABLE" WAS "NYLON" AND "NEOPRENE" WAS "RUBBER". SUPERSEDES DWG. DATED 5/2/80 PER DCN #12944. JMN	DJP	5/23/06

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE **16A & 20A 2 POLE 3 WIRE PIN AND SLEEVE INLETS**

TOLERANCES UNLESS OTHERWISE SPECIFIED		WIRING DEVICE–KELLEMS HUBBELL INCORPORATED BRIDGEPORT, CT	
FRACTIONS	± 1/64	DR. BY W.T.C.	APP. BY DJP
DECIMALS	± .005	TR. BY JMN	SCALE NONE
ANGLES	± 2°	CHK'D BY DJP	DATE 5/23/06

DIMENSION SHEET FOR CAT. NO. SEE TABLE

REPAIRABLE ☐ NON-REPAIRABLE ☒

B

M-6054

3