


M-7279 3



| CAT. NO. | CONFIGURATION | RATING | IEC RATING COLOR | UL | CSA |
|-----------|---------------|------------|------------------|-----|-----|
| HBL4729CA | NEMA 5-15P | 15A. 125V. | YELLOW | YES | YES |

| LIST OF PARTS | | |
|-----------------|---------------|-----------|
| DESCRIPTION | MATERIAL | FINISH |
| COVER | NYLON | BLACK |
| CORD CLAMP | POLYCARBONATE | BLACK |
| CONTACT HOLDER | NYLON | NATURAL |
| RETAINER | LEXAN | CLEAR |
| WIRE CLAMP | .062 CRS | NICKEL PL |
| CONTACTS | BRASS | |
| TRI-DRIVE #8 | BRASS | |
| TERMINAL SCREWS | | |
| TRI-DRIVE | STEEL | ZINC PL |
| ASSEMBLY SCREWS | | |

| REV | DESCRIPTION | APP | DATE |
|-----|--|-----|---------|
| 3 | REVISED VIEWS & CALLOUTS OF SCREWS TO TRI-DRIVE PER DCN #11421 RCM | DVB | 1/27/04 |
| 2 | IN LIST OF PARTS, "POLYCARBONATE WAS "LEXAN"; PER DCN #8988. JAN | CJC | 2/18/02 |
| 1 | "X" REMOVED PER DCN #2940 RCM | JZ | 8/3/94 |

| SYM | REVISIONS | APP | DATE |
|-----|-----------|-----|------|
| | | | |

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE
INSULGRIP ●
2 POLE 3 WIRE
TWIST-LOCK ●
ANGLE CONNECTOR

| | | |
|--|---|---------------------|
| TOLERANCES UNLESS OTHERWISE SPECIFIED FRACTIONS ±1/64 DECIMALS ±.005 ANGLES ±2° | WIRING DEVICE-KELLEMS HUBBELL INCORPORATED BRIDGEPORT, CT | |
| | DR. BY RCM | APP. BY ZIMM |
| | TR. BY | SCALE $\frac{1}{1}$ |
| | CHK'D BY ZIMM | DATE 8/3/94 |

DIMENSION SHEET FOR CAT. NO. SEE TABLE

REPAIRABLE NON-REPAIRABLE

B

M-7279

3