


M-96111



NOTES: (UNLESS OTHERWISE SPECIFIED)

1. DIMENSIONS ARE IN INCHES [MM].
2. DEVICE IS UL LISTED (PRODUCT CATEGORY AXUT) AND CSA CERTIFIED.
3. ELECTRICAL RATING 12A 125V.
4. FOR USE WITH #17 AWG SVT CORD.

CATALOG NO.	COLOR
HBL5867VBLK	BLACK

LIST OF PARTS

DESCRIPTION	MATERIAL	FINISH
HOUSING	NYLON	BLACK
CONTACT BLADE	BRASS	
WIRING CLAMPING NUT	STEEL	NICKEL PL.
BINDING HEAD SCREW	STEEL	COPPER
POLARIZED BLADE	BRASS	NICKEL PL.
BINDING HEAD SCREW	STEEL	NICKEL PL.
CORD CLAMP SCREW	STEEL	BLACK

1	RELEASE PER DCN 12317 MJM	<i>MJM</i>	4/15/05
SYM	REVISIONS	APP	DATE

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE APPLIANCE PLUG  
NEMA 1-15P  
POLARIZED

<del>TOLERANCES UNLESS OTHERWISE SPECIFIED</del> FRACTIONS ± 1/64 DECIMALS ± .005 ANGLES ± 2°	WIRING DEVICE-KELLEMS HUBBELL INCORPORATED BRIDGEPORT, CT	
	DR. BY MJM	APP. BY <i>MJM</i>
	TR. BY	SCALE 1:1
	CHK'D BY <i>MJM</i>	DATE 2/10/05

DIMENSION SHEET FOR CAT. NO. M-96111  
 REPAIRABLE  NON-REPAIRABLE  SEE TABLE B