



CATALOG NUMBER	CONDUCTOR				HOLDING STRENGTH LBS.	DIMENSIONS			CAPPLUGS COLOR CODE	DIE INFORMATION	INSTALLATION TOOLING (#CRIMPS)								
	ACSR		ALUMINUM			B REF.	L REF.	O.D.			MECHANICAL RATCHET			HYDRAULIC			HOLDING STRENGTH OH25 HYTOOL™		
	SIZE	STR.	SIZE	STR.							OUR840	OH25 ⁸	MD6	Y35, Y39, Y750 BAT35, BAT750	Y46 ⁵	Y45 ⁴	CONDUCTOR	HOLDING STRENGTH LBS.	% RATED BREAKING STRENGTH
YSS6R	#6 (.198)	6-1	---	---	900	2.30 [58]	4.72 [120]	.39 [10]	BLUE	162	---	---	W162 (4)	U162 (2)	U162 (2)	U162 (2)	---	---	---
	---	---	#4 SOL. (.204)	1	700												4 7 ALUM.	860	102
YSS4R	#4 (.250) #4 (.257)	6-1 7-1	---	---	1000 1000	1.78 [45]	3.78 [96]	.65 [17]	ORANGE	BG OR 5/8	XBG (6)	(3) (2) (3) (3) (2) (3) (2) (3) (2)	BG (6) WBG (3)	UBG (3)	UBG (3)	UBG (3)	4 5005 ALUM.	1475	102
																	4 5005 ALUM.	1570	105
			#4 STR. (.232) #2 SOL. (.258)	7 1	700 800												4 (6-1) ACSR	1400	77
																	4 (6-1) ACSR	1140	62
																	4 (7-1) ACSR	1510	66
																	4 (7-1) ACSR	1285	56
																	2 SOL. ALUM.	980	85
																	2 SOL. ALUM.	950	83
YSS2R	#2 (.316) #2 (.325)	6-1 7-1	---	---	1600 1600	1.78 [45]	3.78 [96]	.65 [17]	RED	BG OR 5/8	XBG (6)	(3) (2) (3)	BG (6) WBG (3)	UBG (3)	UBG (3)	UBG (3)	2 (6-1) ACSR	1740	63
			#2STR. (.292)	7	1200												2 (7-1) ACSR	1475	42
																	2 (7-1) ACSR	1350	38
																	2 7 ALUM.	1230	97
YSS6RG2	#6 (.198)	6-1	---	---	900	1.78 [45]	4.00 [102]	.65 [17]	BLUE	BG 5/8, OR 243	---	(2)	BG (6) WBG (3)	UBG (3)	UBG (3)	UBG (3)	---	---	---
	---	---	#4 SOL. (.204)	1	700														



- NOTES:
1. MATERIAL: ALUMINUM.
 - 2 MAY BE INSTALLED WITH KEARNEY DIES 5/8, 5/8-1.
 - 3 BARRELS PARTIALLY FILLED WITH PENETROX™ AND SEALED WITH COLOR-CODED CAPPLUGS. (FOR COLOR CODE SEE TABLE).
 - 4 CATALOG #PT6515 ADAPTOR IS REQUIRED TO USE "U" DIES IN Y45 SERIES TOOLS.
 - 5 CATALOG #PUADPI ADAPTOR IS REQUIRED TO USE "U" DIES IN Y46 SERIES TOOLS.
 6. DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED, AND ARE FOR REFERENCE ONLY.
 7. REMOVED PER PCN 3275.
 - 8 WHERE MORE THAN 2 CRIMPS PER END ARE REQUIRED, SLEEVE MUST BE ROTATED 180° AFTER EACH CRIMP.

REFERENCE: SD33889 N21, SE45717

TO ORDER BURNDY® PRODUCTS CALL UNITED STATES 1-800-346-4175 (LONDONDERRY, NH) CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES) FOR PRODUCT INFO: http://www.burndy.com	SERVICE HYSPLICE™	
	ITEM NO:	N/A
	CAT. NO:	YSS-R (TABLE)
	DRAWN BY:	F.B.A 7/19/54
	CHECKER:	R.C. 7/19/54
	DSN APPVL:	C.PALAGI 1/12/95
	MFG APPVL:	---
	QA APPVL:	D.VARIO 1/25/95
	MKT APPVL:	L.HERRON 1/21/95
	PROD FAM:	overhead_bare_conns
PROJECT #:	---	
DOCUMENT TYPE:	Sales	
REL LEVEL:	Released	
DRAWING NO:	SC031169-01	
SCALE:	1:1	
REV:	A	

REV: PE0200