



CSL Striplight

CCL Center-Lens Troffer

CWP Wrap Luminaire



Simple. Reliable. Convenient.

tradeSELECT®



- Simple fluorescent replacement
- Readily available in stock
- Affordably priced
- Utility rebate friendly
- User-friendly with access to LED boards and drivers from below
- Choice of two LED color temperatures
- Familiar shapes, sizes, and appearances for simplicity of use

CSL Striplight

- 4,000 and 8,000 lumens
- Up to 112 lumens per watt
- 3500K or 4000K CCT
- 0-10V dimming, standard
- Fully assembled for quick installation
- Frosted acrylic lens
- Wide range of applications
- Surface mount on wall or ceiling
- Universal voltage (120-277V)
- 80+ CRI
- DLC® (DesignLights Consortium) Qualified - see www.designlights.org

CCL Center-Lens Troffer

- 3,300 and 5,000 lumens
- Up to 118 lumens per watt
- 3500K or 4000K CCT
- 0-10V dimming, standard
- Fully assembled for quick installation
- Frosted acrylic lens
- Emergency battery backup available¹
- 5-wire flex available¹
- Recessed mount
- Universal voltage (120-277V)
- 80+ CRI
- IC Rated
- DLC® (DesignLights Consortium) Qualified - see www.designlights.org

CWP Wrap Luminaire

- 4,000 lumens
- Up to 124 lumens per watt
- 3500K or 4000K CCT
- 0-10V dimming, standard
- Fully assembled for quick installation
- Frosted acrylic lens
- Wide range of applications
- Ceiling mount
- Universal Voltage (120-277V)
- 80+ CRI
- DLC® (DesignLights Consortium) Qualified - see www.designlights.org

CSL ORDERING INFORMATION

Catalog Number	Description	Lumens	Watts	LPW	Qty on Pallet
CSL4-4035	4ft LED Striplight, 4,000 Lumens, 3500K, 0-10V dimming	4231	40	105	120
CSL4-4040	4ft LED Striplight, 4,000 Lumens, 4000K, 0-10V dimming	4517	40	112	120
CSL8-8035	8ft LED Striplight, 8,000 Lumens, 3500K, 0-10V dimming	8460	81	105	120
CSL8-8040	8ft LED Striplight, 8,000 Lumens, 4000K, 0-10V dimming	9036	81	112	120

CCL ORDERING INFORMATION

Catalog Number	Description	Lumens	Watts	LPW	Qty on Pallet
CCL22-3335	2 x 2 Center Lens LED Troffer, 3,300 Lumens, 3500K	3223	29	112	40
CCL22-3335-C588	2 x 2 Center Lens LED Troffer, 3,300 Lumens, 3500K, 5-Wire Flex ¹				
CCL22-3335-ELL14	2 x 2 Center Lens LED Troffer, 3,300 Lumens, 3500K, 1400lm Battery Pack ¹				
CCL22-3340	2 x 2 Center Lens LED Troffer, 3,300 Lumens, 4000K	3345	29	116	40
CCL22-3340-C588	2 x 2 Center Lens LED Troffer, 3,300 Lumens, 4000K, 5-Wire Flex ¹				
CCL22-3340-ELL14	2 x 2 Center Lens LED Troffer, 3,300 Lumens, 4000K, 1400lm Battery Pack ¹				
CCL24-5035	2 x 4 Center Lens LED Troffer, 5,000 Lumens, 3500K	5001	44	114	20
CCL24-5035-C588	2 x 4 Center Lens LED Troffer, 5,000 Lumens, 3500K, 5-Wire Flex ¹				
CCL24-5035-ELL14	2 x 4 Center Lens LED Troffer, 5,000 Lumens, 3500K, 1400lm Battery Pack ¹				
CCL24-5040	2 x 4 Center Lens LED Troffer, 5,000 Lumens, 4000K	5191	44	118	20
CCL24-5040-C588	2 x 4 Center Lens LED Troffer, 5,000 Lumens, 4000K, 5-Wire Flex ¹				
CCL24-5040-ELL14	2 x 4 Center Lens LED Troffer, 5,000 Lumens, 4000K, 1400lm Battery Pack ¹				

Accessories (Order Separately)

FK22	2' x 2' Single Flange Kit (Shipped separately)
FK24	2' x 4' Single Flange Kit (Shipped separately)

¹ Not stocked; ships in 5-10 days

CWP ORDERING INFORMATION

Catalog Number	Description	Lumens	Watts	LPW	Qty on Pallet
CWP4-4035	4ft LED Wrap, 4,000 Lumens, 3500K, 0-10V dimming	4584	37	124	33
CWP4-4040	4ft LED Wrap, 4,000 Lumens, 4000K, 0-10V dimming	4584	37	124	33