



Residential Floor Box Delivery Systems

For Wood Sub-Floors

RACO wood floor boxes allow for the placement of electrical power and voice/data devices to provide lighting, entertainment equipment and computers for family rooms and offices.



UL LISTED Floor Box 232A

ROUND, NONMETALLIC DROP-IN FLOOR BOX

- Industry leading 16.0 cu. in. wiring capacity
- Allows for 15A or 20A with feed through capability
- For power or data applications
- Tamper-resistant receptacle included
- Self leveling, easy screw fastening
- Solid brass cover and flange

Cat. No.	Description	Ship Carton Qty	Pack Qty	Display Carton Dimensions (L x W x H)	UPC-A Bar Code
6RF151SR	Round Drop-in, Brass	6	1	3.55 x 3.50 x 8.25	050169953570




UL LISTED Floor Box 232A



ROUND, CAST IRON FLOOR BOX

- Meets UL514A scrubwater standard for floor boxes
- Durable cast iron
- Gray powder coat paint insid and otut for additional corrosion resistance
- Traditional flip-lid cover design
- 1/2" hubs on bottom of box
- Tamper resistant duplex receptacle sold separately
- Solid brass cover and flange

Cat. No.	Description	Ship Carton Qty	Pack Qty	Display Carton Dimensions (L x W x H)	UPC-A Bar Code
6224	Round, Brass	4	1	6.00 x 4.25 x 6.00	050169062241
6223	Round, Brass	4	1	12.37 x 9.00 x 6.12	050169062234



UL LISTED Floor Box 232A



ROUND, RECESSED FLOOR BOX

- Removable neoprene gaskets allow for independent use of either side of the receptacle with the cover closed
- Tamper-resistant 15A duplex receptacle included
- Back and inside knockouts for proper wiring access
- Recessed receptacle minimizes plug protrusion allowing furniture to be located over the plug
- Brass or nickel plated cover with pre-assembled flange

Cat. No.	Description	Ship Carton Qty	Pack Qty	Display Carton Dimensions (L x W x H)	UPC-A Bar Code
6239BK	Round, Black	1	1	5.60 x 5.60 x 5.30	050169947128
6239BP	Round, Brass	1	1	5.60 x 5.60 x 5.30	050169947135
6239NI	Round, Nickel	1	1	5.60 x 5.60 x 5.30	050169947142
6239SS	Round, Stainless Steel	1	1	5.60 x 5.60 x 5.30	050169947159

NEW, Recessed Floor Boxes with Power and USB Charging, OneType A and One Type C

6239ACBP	Round, Brass	1	1	5.60 x 5.60 x 5.30	050169993545
6239ACNI	Round, Nickel	1	1	5.60 x 5.60 x 5.30	050169993231
6239ACBK	Round, Black Paint	1	1	5.60 x 5.60 x 5.30	050169993224



UL LISTED Floor Box 232A

RECTANGULAR, METALLIC FLOOR BOX

- Contains low profile duplex receptacle
- Meets 50514A scrubwater standard for floor boxes
- Tamper-resistant 15A receptacle included
- Watertight assembly
- Polished brass finish with two threaded plugs

Cat. No.	Description	Ship Carton Qty	Pack Qty	Display Carton Dimensions (L x W x H)	UPC-A Bar Code
6500BR-5	Rectangular, Brass	10	1	3.25 x 5.25 x 4.75	050169953150
6500NI-5	Rectangular, Nickel	10	1	3.25 x 5.25 x 4.75	050169953167





Residential Floor Box Delivery Systems

For Concrete Slab

RACO round nonmetallic floor box offers a traditional and economical solution for electrical power or a combination of power and voice/data. For residential or commercial use.



ROUND, NONMETALLIC FLOOR BOX

- Minimum depth of pour - 3 inches
- Multi service capability for power and voice/data
- PVC floor box is easily cut after pour for height adjustment

Cat. No.	Description	Ship Carton Qty	Pack Qty	Display Carton Dimensions (L x W x H)	UPC-A Bar Code
5511	Round, Concrete Box (Brass cover sold separately)	4	1	6.875 x 7.50 x 6.00	050169055113



ROUND, SOLID BRASS FLOOR BOX COVER

- Solid Brass material
- Meets UL514A Scrubwater Standard for floor boxes
- Meets UL 300 Lb. load (weight) rating

Cat. No.	Description	Ship Carton Qty	Pack Qty	Display Carton Dimensions (L x W x H)	UPC-A Bar Code
RAC5500KIT	Round, Brass Cover kit	10	1	6.375 x 6.50 x 3.750	050169953587



FLOOR BOX COVER, ASSEMBLY KITS

- Nonmetallic covers are made from a high impact, corrosion resistant thermoplastic material
- Meets UL514A Scrubwater Standard for floor boxes
- Meets UL 300 Lb. load (weight) rating

Cat. No.	Description	Ship Carton Qty	Pack Qty	Display Carton Dimensions (L x W x H)	UPC-A Bar Code
6299	Adapter, Round, Gray Nonmetallic Cover Kit	10	1	6.50 x 6.50 x 3.750	050169062999