



Full-Range Dimming Control for Precise Operation

The new Rocker Slide Dimmers and Preset Slide Dimmer feature preset ON/OFF switching and smooth, slide-action, full-range dimming for incandescent, dimmable LEDs, dimmable CFLs, halogen, magnetic low voltage (MLV), electronic low voltage (ELV) and fluorescent loads. All dimmers come packaged in White with Ivory and Light Almond color change kits. Additional color change kits are available in Black, Brown, Red and Gray.

Features

- Separate ON/OFF switch that preserves the selected brightness level
- Provide single pole (one location) or 3-way (two location) lighting control
- Slim, compact housing fits easily into a standard wallbox
- Suitable for multi-gang installations
- Built-in radio/TV interference filter
- UL1472, cCSAus, Certified to Standard 184.1, NOM 057
- 5 year warranty



Preset Slide Dimmer



Rocker Slide Dimmers

Ordering Information

Rocker Slide Dimmer

Ordering Example: RSD710-UNV-WVL

MODEL		COLOR	
RSD710-UNV	Rocker-Slide Dimmer for Fluorescent Ballast and LED Power Supply, 0-10V Dimming, 1200VA@120VAC, 1500VA@277VAC, 60Hz, Single Pole or 3-Way, Suitable for use with Class 1 or Class 2 wiring - White, Ivory & Light Almond	WVL	White with Ivory & Light Almond Color Change Kits
RSDL06-120	Rocker-Slide Dimmer for Dimmable LED, CFL and Incandescent, Locator Light, 600W@120VAC Incandescent, 300W@120VAC Dimmable LED and CFL, 60Hz, Single Pole or 3-Way - White, Ivory & Light Almond		
RSDE06-120	Rocker-Slide Dimmer for Electronic Low Voltage, Dimmable LED and CFL, 600VA@120VAC Electronic Low Voltage, 300W@120VAC Dimmable LED and CFL, 60Hz, Neutral Required, Single Pole or 3-Way - White, Ivory & Light Almond		
RSDM10-120	Rocker-Slide Dimmer for MLV, Incandescent, Dimmable LED and CFL, Locator Light, 1000VA@120VAC MLV, 1000W@120VAC, Incandescent, 450W@120VAC Dimmable LED and CFL, 60Hz, Single Pole or 3-Way - White, Ivory & Light Almond		

COLOR KIT MODEL		COLOR	
RSDKIT-LL	Rocker-Slide Dimmer Color Change Kit for RSDM10/RSDL06 Dimmers, Locator Light	WH	White
RSDKIT-NL	Rocker-Slide Dimmer Color Change Kit for RSD710/RSDE06 Dimmers	IV	Ivory
		LA	Light Almond
		GY	Gray
		BK	Black
		BN	Brown
		RD	Red

Preset Slide Dimmer

Ordering Example: PSD710-UNV-WVL

MODEL		COLOR	
PSD710-UNV	Preset Slide Dimmer for 0-10V LED Drivers and Fluorescent Ballasts, Single Pole or 3-Way, 1200-1500VA 120/277VAC	WVL	White with Ivory & Light Almond Color Change Kits

COLOR KIT MODEL		COLOR	
PSDKIT-LL	Preset-Slide Dimmer Color Change Kit for PSD710 Dimmer	WH	White
		IV	Ivory
		LA	Light Almond
		GY	Gray
		BK	Black
		BN	Brown
		RD	Red

Note: Wallplates not included